

Data Sheet

HAL/HAR 3930-410x

Stray-Field Robust 3D Position Sensor
with Digital Output Interfaces

3D | HAL
Technology

master | HAL
Technology

Copyright, Warranty, and Limitation of Liability

The information and data contained in this document are believed to be accurate and reliable. The software and proprietary information contained therein may be protected by copyright, patent, trademark and/or other intellectual property rights of TDK-Micronas. All rights not expressly granted remain reserved by TDK-Micronas.

TDK-Micronas assumes no liability for errors and gives no warranty representation or guarantee regarding the suitability of its products for any particular purpose due to these specifications.

By this publication, TDK-Micronas does not assume responsibility for patent infringements or other rights of third parties which may result from its use. Commercial conditions, product availability and delivery are exclusively subject to the respective order confirmation.

Any information and data which may be provided in the document can and do vary in different applications, and actual performance may vary over time.

All operating parameters must be validated for each customer application by customers' technical experts. Any mention of target applications for our products is made without a claim for fit for purpose as this has to be checked at system level.

Any new issue of this document invalidates previous issues. TDK-Micronas reserves the right to review this document and to make changes to the document's content at any time without obligation to notify any person or entity of such revision or changes. For further advice please contact us directly.

Do not use our products in life-supporting systems, military, aviation, or aerospace applications! Unless explicitly agreed to otherwise in writing between the parties, TDK-Micronas' products are not designed, intended or authorized for use as components in systems intended for surgical implants into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the product could create a situation where personal injury or death could occur.

No part of this publication may be reproduced, photocopied, stored on a retrieval system or transmitted without the express written consent of TDK-Micronas.

TDK-Micronas Trademarks

- HAL
- HAR
- 3D HAL
- masterHAL

Third-Party Trademarks

All other brand and product names or company names may be trademarks of their respective companies.

License Note

HAL/HAR 3930 uses licenses of Fraunhofer Institute for Integrated Circuits IIS.

Contents

Page	Section	Title
5	1.	Introduction
6	1.1.	Major Applications
7	1.2.	Features
8	2.	Ordering Information
8	2.1.	Device-Specific Ordering Codes
10	3.	Functional Description
10	3.1.	General Function
13	3.2.	Signal Path
14	3.3.	Register Definition
14	3.3.1.	RAM Registers
16	3.3.2.	EEPROM Registers
30	3.4.	SENT Output Protocol
32	3.4.1.	H.1 Format: 6 Data Nibble Frame with Two Fast Channels
33	3.4.2.	H.2 Format: 3 Data Nibble Frame with One Fast Channel
34	3.4.3.	H.4 Format: Secure Single Sensors with 12-bit Fast Channel
35	3.4.4.	Error Diagnostic Reporting on Fast Channel and Status Bits
36	3.4.5.	Pause Pulse
36	3.4.6.	CRC Implementation
36	3.4.7.	Slow Channel: Enhanced Serial Message
37	3.4.8.	Slow Channel: Serial Message Sequence
38	3.4.9.	Slow Channel: Serial Message Error Codes
38	3.4.10.	Start-Up Behavior
38	3.4.11.	Message Time for SENT Frames in PPC Mode
39	4.	Functional Safety
39	4.1.	Functional Safety Manual and Functional Safety Report
39	4.2.	Integrated Diagnostic Mechanisms
41	5.	Specifications
41	5.1.	Outline Dimensions
45	5.2.	Soldering, Welding, Assembly
45	5.3.	Storage and Shelf Life Package
45	5.4.	Size and Position of Sensitive Areas
46	5.5.	Definition of Magnetic-Field Vectors
47	5.6.	Pin Connections and Short Description
49	5.7.	Absolute Maximum Ratings
50	5.8.	Recommended Operating Conditions
52	5.9.	Characteristics
59	5.10.	Magnetic Characteristics
63	5.11.	Temperature Sensor

Contents, continued

Page	Section	Title
64	6.	Application Notes
64	6.1.	Ambient Temperature
64	6.2.	EMC and ESD
65	6.3.	Application Circuits
67	6.4.	Recommended Pad Size
68	7.	Programming of the Sensor
68	7.1.	Programming Interface
69	7.2.	Programming Environment and Tools
69	7.3.	Programming Information
70	8.	Document History

Stray-Field Robust 3D Position Sensor with Digital Output Interfaces

Release Note: Revision bars indicate significant changes to the previous edition.

1. Introduction

HAL/HAR 3930-410x represents the second generation of the HAL/HAR 3930 family. HAL/HAR 3930-410x further extends TDK-Micronas' 3D position sensor family addressing the need for stray-field robust 2D position sensors (linear and angular) as well as the ISO 26262 compliant development. HAR 3930-410x is the dual-die version of the HAL 3930-4100. It provides full redundancy due to two independent dies stacked in a single package, each electrically connected to the pins of one package side. The stacked-die architecture ensures that both dies occupy the same magnetic-field position, thus generating synchronous measurement signals. It is a high-resolution position sensor for highly accurate position measurements.

HAL/HAR 3930 features PWM or SENT outputs. The digital output format is customer configurable. In SENT mode, the sensor transmits SENT messages with and without pause pulse according to SAE J2716 rev. 4. Many parameters like tick time, frame format, etc. are configurable by the customer. The PWM output is configurable with frequencies between 0.1 kHz and 2 kHz.

Additionally, the sensor offers a switch output (configurable high-/low-side switch). The switch signal is derived from the calculated position information or from various other sources along the device's signal path (e.g. temperature, magnetic-field amplitude, etc.). It is possible to define on/off switching points, switch logic, and switch polarity.

The device can measure 360° angular range, linear movements, as well as 3D position information of a magnet. 3D position means two angles calculated out of $B_x/B_y/B_z$. The 3D position information can be transmitted via the SENT or two PWM outputs. The device also features a so-called modulo function mainly used for chassis position sensor applications. With this mode it is possible to split the 360° measurement range into sub-segments (90°, 120° and 180°).

The HAL/HAR 3930 measures, based on Hall technology, vertical and horizontal magnetic-field components. It is able to suppress external magnetic stray-fields by using an array of Hall plates. Only a simple two-pole magnet is required to measure a rotation angle. Ideally, the magnet should be placed above the sensitive area in an end-of-shaft configuration. Stray-field robust off-axis measurements are supported as well.

On-chip signal processing calculates up to two angles per die out of the magnetic-field components and converts this value into a digital output signal. Major characteristics like gain and offset, reference position, etc. can be adjusted to the magnetic circuitry by programming the non-volatile memory.

HAL/HAR 3930 is defined as SEooC (Safety Element out of Context) ASIL C ready according to ISO 26262 and can be integrated in automotive safety-related systems up to ASIL D.

The device is designed for automotive and industrial applications in the ambient temperature range from $-40\text{ }^{\circ}\text{C}$ to $150\text{ }^{\circ}\text{C}$. The sensor is available in an SOIC8 SMD package as a single-die device and in an SSOP16 SMD package for the dual-die version.

1.1. Major Applications

Thanks to the sensor's versatile programming characteristics and its high accuracy, the HAL/HAR 3930 is a potential solution for the following application examples:

- Accelerator pedals
- Valve position, e.g. throttle
- Shift position
- Steering angle
- Non-contact potentiometer
- Clutch position
- Transmission position detection
- Brake pedal position / brake stroke sensor

1.2. Features

- Accurate angular measurement up to 360° and linear position detection
- 3D position detection supporting transmission of two angles out of B_X , B_Y , B_Z
- Compensation of magnetic stray-fields (rotary or linear position detection)
- SEooC ASIL C ready according to ISO 26262 to support Functional Safety applications
- Wide supply voltage range of 3 V up to 18 V
- Customer-configurable PWM or SENT output (push-pull output & open-drain output)
- Configurable output slew rates to reduce EMC emission
- 0.1 kHz to 2 kHz PWM
- Two parallel PWM outputs for the transmission of two angles
- SENT according to SAEJ2716 rev. 4 (APR2016) supporting three different frame formats:
 - H1. format: Two 12-bit fast channels (3 data nibbles position information and 3 data nibbles second position information or 12-bit temperature or magnetic-field amplitude) (supporting A.1 Dual Throttle Position Sensors)
 - H.2 Format: One 12-bit fast channel (3-nibble position information)
 - H.4 Format: Secure single sensors with 12-bit fast channel (3 nibble position information) and 12-bit secure sensor information
 - Enhanced 12-bit serial message format including temperature information
 - Programmable tick times between 0.5 μ s and 12 μ s
 - Low time of 3, 5, and 6 ticks
 - Configurable pause pulse (PPC, NPP)
 - Transmission of OEM IDs via slow channel
- Additional switch output with customer-configurable switching levels
- Up to 8 kSps sampling frequency
- Operates from –40 °C up to 170 °C junction temperature
(Max. Ambient Temperature: $T_{A,absmax} = 160$ °C; depending on used supply voltage)
- Programming via the sensor's output pin. No additional programming pin required
- Various configurable signal processing parameter, like output gain and offset, reference position, temperature dependent offset, etc.
- Modulo function (90°/120°/180°) for chassis position applications
- Programmable arbitrary output characteristic with 17 variable or 33 fixed setpoints
- Programmable characteristics in a non-volatile memory (EEPROM) with redundancy and lock function
- Read access on non-volatile memory after customer lock

2. Ordering Information

A TDK-Micronas device is available in a variety of delivery forms. They are distinguished by a specific ordering code:




Fig. 2–1: Ordering code principle

For a detailed information, please refer to the brochure: “Sensors and Controllers: Ordering Codes, Packaging, Handling”.

2.1. Device-Specific Ordering Codes

The HAL/HAR 3930 is available in the following packages.

Table 2–1: Available packages



Package Code (PA)	Package Type
DJ	SOIC8
GU	SSOP16

For available variants Packaging (P), Quantity (Q), and Special Procedure (SP) please contact TDK-Micronas.

Table 2–2: Ordering Information & version overview

Product	Package	Configuration Version	Further Code [P-Q-SP]	Comments
HAL 3930	DJ = SOIC8	94xy	See TDK-Micronas Ordering Information	94xy versions can be engineering samples or qualifiable devices (not available for production)
HAL 3930	DJ = SOIC8	4100	See TDK-Micronas Ordering Information	Production version
HAR 3930	GU = SSOP16	94xy	See TDK-Micronas Ordering Information	94xy versions can be engineering samples or qualifiable devices (not available for production)
HAR 3930	GU = SSOP16	4100	See TDK-Micronas Ordering Information	see note below
HAR 3930	GU = SSOP16	4101	See TDK-Micronas Ordering Information	Production version
Note: HAR 3930GU-4100 is not recommended for new designs especially if 6Z & 6ZD measurement mode is intended to be used. For these two modes it is possible that the device indicates sporadic errors which are not related to real errors. It is recommended to filter error indications transmitted by the device. Only errors that are persistent within the fault handling interval of 5 ms should be acknowledged by the upper level micro controller or ECU. It is recommended to use HAR 3930GU-4101 instead which is not showing the about mentioned behavior.				

Table 2–3: Available ordering codes and corresponding package marking

Ordering Code	Package Marking	Description
HAL3930DJ-4100[P-Q-SP]		Line 1: Product Type / Configuration-ID Line 2: Lot number Line 3: Date code / Special Procedure SP (optional)
HAR3930GU-4101[P-Q-SP]		Line 1: Product Type / Configuration-ID Line 2: Lot number Line 3: Date code / Special Procedure SP (optional)
Example: HAR3930GU-4101R-8-00		R: Tape & Reel 8: Two reels with 3.5k pcs each 00: No SP

3. Functional Description

3.1. General Function

HAL/HAR 3930 is a 3D position sensor based on Hall-effect technology. The sensor includes an array of horizontal and vertical Hall-plates based on TDK-Micronas' 3D HAL technology. The array of Hall-plates has a diameter C of 2.25 mm (nominal).

The dual-die version HAR 3930 is available in an SSOP16 package. Fig. 3–1 shows the position of the different Hall-plates.




Fig. 3–1: Hall-plate position definition for HAR 3930

Note

Die 2 is rotated by 180° in relation to die 1. Therefore the measurement values of magnetic field X and Y components have opposite signs compared to die 1.

The single-die version HAL 3930 is available in an SOIC8 package. Fig. 3–2 shows the position of the different Hall-plates for HAL 3930.




Fig. 3–2: Hall-plate position definition for HAL 3930

The Hall-plate signals are first measured by up to three A/D converters, filtered and temperature compensated. A linearization block can be used optionally to reduce the overall system angular non-linearity error, due to mechanical misalignment, magnet imperfections, etc.

On-chip offset compensation by spinning current minimizes the errors due to supply voltage and temperature variations as well as external package stress.

Stray-field compensation is done device inherent.

Depending on the measurement configuration different combinations of Hall-plates will be used for the magnetic-field sensing.

The sensor supports various measurement configurations:

- Angular measurements in a range between 0° and 360° with stray-field compensation
- Linear position detection with stray-field compensation based on the differential signals
- 2D linear and angular position detection without stray-field compensation (B_Y/B_X , B_Z/B_X , B_Z/B_Y) with single 3D Pixel Cell (Die 1 & single-Die = Pixel Cell 1 and die 2 = Pixel Cell 2)
- 3D position detection (calculation of two angles) without stray-field compensation

The 360° angular range can be split in 90°/120°/180° sub-segments.

Additionally, the device features a switch output for each die. The source for the switch signal can be derived from various internal sensor signals along the signal path. The available sources can be found in Table 3–1 on page 25. It is possible to define ON and OFF switching levels, the start-up behavior, and the output polarity. The switch output can be configured as high-side or low-side switch.

Overall, the in-system calibration can be utilized by the system designer to optimize performance for a specific system. The calibration information is stored in an on-chip non-volatile memory.

The calculated position information is transmitted either via PWM signals or SENT frames.

The HAL/HAR 3930 is programmable by modulation of the output voltage. No additional programming pin is needed and fast end-of-line programming is enabled.




Fig. 3–3: Example: Block diagram of HAR 3930

3.2. Signal Path

The DSP part of this sensor performs the signal conditioning. The parameters for the DSP are stored in the non-volatile memory. Details of the overall signal path are shown in Fig. 3–4. Not all functions are available for all measurement modes. Depending on the measurement setup, the signal path is scaled to the requirements for the measurement setup.




Fig. 3–4: Signal path example for HAL 3930 or die 1 of HAR 3930

The sensor signal path contains two kinds of registers. Registers that are read-only and programmable registers (non-volatile memory). The **read-only (RAM) registers** contain measurement data at certain steps of the signal path and the **non-volatile memory registers (EEPROM)** change the sensor's signal processing. **EEPROM settings** are individually configurable bits within an EEPROM register.

3.3. Register Definition

Note

Further details about the programming of the device and detailed register setting description as well as memory map can be found in the document: HAL/R 3930-410x User Manual.

3.3.1. RAM Registers

TEMP_ADJ

The TEMP_ADJ register contains already the TDK-Micronas' compensated digital value of the sensor's junction temperature.

COMP_CH1, COMP_CH2 and COMP_CH3

COMP_CH1, COMP_CH2 and COMP_CH3 registers contain the TDK-Micronas' temperature compensated magnetic-field information of channel 1, channel 2 and channel 3. COMP_CH3 is only available for the 3D measurement setups.

AMPLITUDE

The AMPLITUDE register contains sum of squares of the magnetic-field amplitude of all three channels calculated with the following equation. In case of two channels only the first two terms are used. This information is used for the magnet lost detection:

$$\text{AMPLITUDE} = \frac{\text{COMP_CH1}^2}{32768} + \frac{\text{COMP_CH2}^2}{32768} + \frac{\text{COMP_CH3}^2}{32768}$$

PHASE_CORR_CH2, PHASE_CORR_CH3

PHASE_CORR_CHx registers contain the customer compensated magnetic-field information of channel 2 and channel 3 after customer phase-shift error correction using the PHASE_CORRECTION_CHx registers. PHASE_CORR_CH3 is only available for the 3D measurement setups.

CUST_COMP_CH1, CUST_COMP_CH2 and CUST_COMP_CH3

CUST_COMP_CH1, CUST_COMP_CH2 and CUST_COMP_CH3 registers contain the customer compensated magnetic-field information of channel 1, channel 2 and channel 3 used for the angle calculation. These register contain already the customer phase-shift, gain and offset corrected data. CUST_COMP_CH3 is only available for the 3D measurement setups.

ANGLE_OUT_x

The ANGLE_OUT_1 and ANGLE_OUT_2 registers contain the digital value of the position calculated by the angle calculation algorithm. ANGLE_OUT_1 is always available and ANGLE_OUT_2 is a customer configuration option only available for 3D measurements with one pixel cell enabling the calculation of a second angle out of B_x , B_y and B_z .

ANGLE_AMP_x

The ANGLE_AMP_1 and ANGLE_AMP_2 registers contain the digital value of the magnetic-field amplitude calculated by the angle calculation algorithm. ANGLE_AMP_1 is always available and ANGLE_AMP_2 is a customer configuration option only available for 3D measurements with one pixel cell enabling the calculation of a second angle out of B_x , B_y and B_z .

REF_ANGLE_OUT_x

The REF_ANGLE_OUT_x registers contain the digital value of the angle information after setting the reference angle defining the zero angle position.

MODULO_OUT

The MODULO_OUT register contains the digital value of the angle information after applying the modulo calculation algorithm. MODULO_OUT is only available for the primary angle output.

SETPOINT_IN_x

The SETPOINT_IN_x registers contain the digital value of the angle information after the setpoint scaling block and are the values used for the input of the setpoint linearization block.

SETPOINT_OUT_x

The SETPOINT_OUT_x registers contain the digital value of the angle information after the setpoint linearization block.

DNC_OUT

The DNC_OUT register contains the digital value of the angle information after the DNC filter. DNC_OUT is only available for the primary angle output.

OUT_x

The OUT_x registers contain the digital value of the angle information after all signal processing steps and depend on all customer configuration settings.

DIAG_X

The DIAG_0 and DIAG_1 registers report certain failures detected by the sensor. HAL/HAR 3930 performs self-tests during power-up as well as continuous system integrity tests during normal operation. The result of those tests is reported via the DIAG_X registers (further details can be found in see Section 4.2. on page 39).

Micronas IDs

The MIC_ID1 and MIC_ID2 registers are both 16-bit organized. They are read only and contain TDK-Micronas production information, like X,Y position on the wafer, wafer number, etc. This register content will be transmitted via the SENT interface if the serial message channel has been activated.

3.3.2. EEPROM Registers

Application Modes

HAL/HAR 3930 can be configured in different application modes. Depending on the required measurement task one of the application modes can be selected. The register SETUP_FRONTEND (Table 3–2 on page 26) defines the different available modes.

– 6Z-Mode: 180° rotary (stray-field compensated)

This mode uses six horizontal Hall-plates to measure a 180° angular range. It requires a 4-pole magnet. Speciality of this mode is that the device can compensate stray-fields according to ISO 11452-8 definition as well as disturbing gradients generated for example by a current conducting wire. Fig. 3–5 shows the related signal path.




Fig. 3–5: Signal path diagram of 6Z-Mode (stray-field robust 180° measurement)

– 6ZD-Mode: 360° rotary (stray-field compensated)

This mode uses six horizontal Hall-plates to measure a 360° angular range. The differences of opposite Z-Plates are given to each channel (Z4-Z1, Z6-Z3, Z2-Z5). It requires a 2-pole magnet. The device can compensate stray fields according to ISO 11452-8 definition. Fig. 3–6 shows the related signal path.




Fig. 3–6: Signal path diagram for 6ZD-Mode (stray-field robust 360° measurement)

– $\Delta X \Delta Y$ & $\Delta X \Delta Z$ -Mode: Linear movement or off-axis rotary (stray-field compensated)

This mode uses a combination of horizontal and vertical Hall-plates to measure a stray-field compensated linear movement (ΔB_X & ΔB_Z of 3D Pixel Cells 1 and 2). Alternatively, this setup can be used for off-axis stray-field compensated angular measurements in case that a combination of vertical Hall-plates is selected (ΔB_X & ΔB_Y of 3D Pixel Cells 1 and 2). The device can compensate stray-fields according to ISO 11452-8 definition. Fig. 3–7 shows the related signal path for $\Delta X \Delta Y$ setup and Fig. 3–8 the signal path for $\Delta X \Delta Z$ setup.




Fig. 3–7: Signal path diagram for $\Delta X \Delta Y$ -Mode (stray-field robust off-axis position detection)




Fig. 3–8: Signal path diagram for $\Delta X\Delta Z$ -Mode (stray-field robust linear position detection)

For the linear movement setup the angle calculation is done by using the following equation:

$$\alpha = \text{ATAN2}(\Delta B_Z, \Delta B_X)$$

For the off-axis rotary setup the angle calculation is done by using the following equation:

$$\alpha = \text{ATAN2}(\Delta B_Y, \Delta B_X)$$

– $\Delta X\Delta Z$ -Mode: Linear movement (stray-field compensated; HAR 3930-4101 only)

This mode uses a combination of horizontal and vertical Hall-plates to measure a stray-field compensated linear movement (ΔB_X of 3D Pixel Cells 1 and 2 and ΔB_Z out of $Z2+Z6$ and $Z3+Z5$). The device can compensate stray-fields according to ISO 11452-8 definition. Fig. 3–9 shows the related signal path.




Fig. 3–9: Signal path diagram for $\Delta X\Delta Z$ - Mode (stray-field robust linear position detection)

The angle calculation is done by using the following equation:

$$\text{ALPHA} = \text{ATAN2}(\Sigma \text{BZ53} - \Sigma \text{BZ62}, \Delta \text{BX})$$

– 2D-Mode (XY, XZ, YZ): 360° rotary or linear movement measurement without stray-field compensation

This mode uses horizontal and vertical Hall-plates to measure B_X , B_Y , B_Z (Pixel 1 for HAL 3930 and Die of HAR 3930. Pixel 2 for Die 2 of HAR 3930). The angle will be calculated out of combinations of B_Y/B_X , B_Z/B_X or B_Z/B_Y . This mode does not compensate stray-fields. The measurement setup is similar to the well known HAL 37xy family from TDK-Micronas.




Fig. 3–10: Signal path diagram for 2D-Mode (rotary or linear position detection w/o stray-field compensation)

– 3D-ATAN2-Mode: 3D measurement with calculation of two angles (ARCTAN2 calculation)

These modes use horizontal and vertical Hall-plates to measure B_X , B_Y , B_Z (Pixel 1 for HAL 3930 and Die of HAR 3930. Pixel 2 for Die 2 of HAR 3930). The angle will be calculated out of combinations of B_Z/B_X and B_Z/B_Y .

The angle calculation is done by using the following equations:

$$\alpha = \text{ATAN2}(B_Z, B_X)$$

$$\beta = \text{ATAN2}(B_Z, B_Y)$$

Both calculated angles are sent via PWM (two separate outputs) or SENT interface by using the H.1. format (Table 3–7 on page 33). See Fig. 3–4 for detailed signal path.

– 3D-Joystick-Mode: 3D measurement with calculation of two angles (joystick equation)

This mode uses horizontal and vertical Hall-plates to measure B_X , B_Y , B_Z (Pixel 1 for HAL 3930 and Die of HAR 3930. Pixel 2 for Die 2 of HAR 3930). The angle will be calculated by a special equation optimized for “joystick” setups. This mode does not compensate any stray fields.

The angle calculation is done by using the following equations:

$$\text{ALPHA} = \text{ATAN}\left(\frac{\sqrt{\text{CUST_COMP_CH1}^2 + (\text{JOYSTICK_KT} \times \text{CUST_COMP_CH3})^2}}{\text{CUST_COMP_CH2}}\right)$$

$$\text{BETA} = \text{ATAN}\left(\frac{\sqrt{\text{CUST_COMP_CH1}^2 + (\text{JOYSTICK_KT} \times \text{CUST_COMP_CH2})^2}}{\text{CUST_COMP_CH3}}\right)$$

Both calculated angles are sent via PWM (two separate outputs) or SENT interface by using the H.1. format (Table 3–7 on page 33).




Fig. 3–11: Signal path diagram for 3D-ATAN2 & 3D-Joystick-Modes (3D measurement setup)

JOYSTICK_KT

The equation for the angle calculation in 3D-Joystick-Mode is using a gain factor JOYSTICK_KT. JOYSTICK_KT is a 16 bit register.

Customer IDs

The customer ID registers (CUSTOMER_ID0 to CUSTOMER_ID9) consist of ten 16-bit words and can be used to store customer production information, like serial number or project information for PWM output. Additionally they are used to code SENT slow channel information like OEM codes, sensor type information and fast channel transfer characteristics. The customer IDs will be part of the SENT slow channel in case that the SENT output is activated and transmission via slow channel is selected as well. Please see Table 3–13 on page 37 for further details.

Magnetic Range Check

The magnetic range check uses the AMPLITUDE register value or the ANGLE_AMP_1 register and compares it with an upper and lower limit threshold defined by the customer programmable registers MAG_LOW and MAG_HIGH. If either low or high limit is exceeded, the sensor will indicate an error. The selection between the source (AMPLITUDE or ANGLE_AMP_1 register) can be made with SETUP_FRONTEND register bit 11 (Table 3–2 on page 26).

Mag-Low Limit

MAG_LOW defines the low level for the magnetic-field range check function.

Mag-High Limit

MAG-HIGH defines the high level for the magnetic-field range check function.

MAG_LOSS_OUTPUT

The MAG_LOSS_OUTPUT register has two different functions depending on the selected output format.

The device will transmit the register value as PWM duty-cycle in case of magnet loss detection (AMPLITUDE is below the Mag-Low limit). The 12 LSB's are used for the 2kHz PWM frequency and the 13 LSBs for all other frequencies. Default value is (0x0FAD = 98% for the 12 bit value).

The device will send the 12 LSB's of this register in case of an activated SENT output and if the bit sent_mag_loss of the SETUP_PROTOCOL register has been set to one.

Phase Correction

PHASE_CORRECTION_CH12 and PHASE_CORRECTION_CH13 can be used to compensate a phase shift of channel 2 and channel 3 in relation to channel 1.

Neutral value for the registers is zero (no phase-shift correction).

Low-Pass Filter

With the LOW_PASS_FILTER register it is possible to select different –3 dB frequencies for HAR 3930. The default value is zero (low pass filter disabled). The filter frequency is valid for all channels.

OFFSET_CHx_0...2

OFFSET_CH1_0...2, OFFSET_CH2_0...2 and OFFSET_CH3_0...2 support three polynomials of second order and describe the temperature compensation of the offset of channel 1, channel 2, and channel 3 (compensating a remaining offset in each of the three channels). This means a constant, linear and quadratic offset factor can be programmed for up to three channels (temperature dependent offset).

GAIN_CHx_0...2

GAIN_CH1_0...2, GAIN_CH2_0...2 and GAIN_CH3_0...2 support three polynomials of second order and describe the temperature compensation of the sensitivity of channel 1, channel 2 and channel 3 (compensating the amplitude mismatches between three channels). This means a constant, linear and quadratic gain factor can be programmed individually for the three channels (temperature dependent gain).

Reference Angle Position

The output signal zero position defines the reference position for the angle output and therefore it is possible to shift the discontinuity point in the output characteristics out of the measurement range with these parameters. It can be set to any value of the angular range.

REF_ANGLE_0...2_CH1 defines a polynomial of second order with REF_ANGLE_0_CH1 (constant part), REF_ANGLE_1_CH1 (linear part) and REF_ANGLE_2_CH1 (quadratic part). REF_ANGLE_CH2 is a temperature independent (constant factor) and only available in case that the secondary channel is activated.




Fig. 3–12: Example definition of zero degree point

Modulo Select

HAL/HAR 3930 can split the 360° measurement range into sub-ranges of 90°, 120° and 180°. For example in the 90° sub-range output signal is repeating after 90°. The MODULO register can be used to select between these four different output ranges. Modulo function can only be applied on the primary output channel.

The desired modulo calculation can be selected by setting certain bits in the SETUP_FRONTEND register.

nmult_x (EEPROM Setting)

nmult_1 and nmult_2 define the gain exponent for the setpoint scaling block on the data channel. The factor is multiplied by SP_GAIN_CHx to achieve gain factors up to 128. (SETUP_DATAPATH[11:9] bits (= nmult_2), SETUP_DATAPATH[7:5] bits (= nmult_1).

Setpoint Gain

SP_GAIN_CH1 and SP_GAIN_CH2 define the output gain for the primary and secondary data channels. They are used to scale the position information to the input range of the linearization block. SP_GAIN_CH2 is only available for modes with a calculation of a secondary angle.

Setpoint Offset

SP_OFFSET_CH1 and SP_OFFSET_CH2 define the output offset for the primary and secondary data channels. SP_OFFSET_CH2 is only available for modes with a calculation of a secondary angle.

Setpoint Linearization

The setpoint linearization block enables the linearization of the sensor's output characteristic for the customer's application. It consists of 33 setpoints (SP0, SP1, ..., SP32) or 34 setpoints for two channels (17 setpoints each data channel; two times SP0, SP1, ..., SP16). Each setpoint is defined by its fixed x position and its programmable y value. The setpoint x positions (SP(n)_X) are equally distributed between -32768...32767 LSB along the signal range.

The setpoint registers have a length of 16 bits and are two's complement coded. Therefore the setpoint y values (SP(n)_Y) can vary -32768...32767 LSB.

Alternatively 17 variable setpoints can be used. In this case 15 x positions and 17 setpoint y values (the first corresponds to position -32768 and the last to 32767) are freely programmable.

The SETUP_DATAPATH[0] bit (= variable setpoints) selects between 33 fixed and 17 variable setpoints. SETUP_FRONTEND[12] bit (= setpoint_type) defines the option to store the y values as absolute values or differentially to their setpoint x positions.

The setpoint register values are initially set to 0 (neutral) by default. The setpoint linearization block works in a way that the incoming signal (SETPOINT_IN_x value) is interpolated linearly between two adjacent setpoints (SP(n) and SP(n+1)). The resulting SETPOINT_OUT_x register value represents the angular information after the setpoint scaling.

In case of variable setpoints are selected nspgain_x (nspgain_1 & nspgain_2) registers must be used.

nspgain_x (EEPROM Settings)

The SETUP_DATAPATH[15:12] bits (= nspgain_2) and SETUP_DATAPATH[4:1] bits (= nspgain_1) set the gain exponent for the setpoint slope on data channel 1 and 2. With the 4 bits it is possible to get gains up to 65536.

DNC Filter Registers (dnc_–3dB_frequency & dnc_threshold)

The DNC (Dynamic Noise Cancellation) filter decreases the output noise significantly by adding a low-pass filter with a very low cut-off frequency for signals below a certain signal change threshold (dnc_threshold, DNC[15:8]). The attenuation factor dnc_–3dB_frequency of this IIR filter can be selected by the bits DNC[7:0] of the DNC registers. Both parameters have a length of 8 bits.

Signals with a very low amplitude (signals classified as noise e.g. $\pm 0.5^\circ$) and periodic movements with an amplitude lower than 1° will be filtered whereas signals with a higher amplitude are untouched (i. e. rapid movements). The activation of the DNC filter has no impact on the resolution of the output and does not add any additional processing delay.

For dnc_threshold only values from 0 to 255 are allowed. For the dnc_–3dB_frequency only cutoff frequencies up to 50% of the sample frequency ($0.5 \times f_{\text{dec sel}}$) are allowed. To disable the DNC filter both registers must be set to 0.

OUT_OFFSET_CHx

The registers OUT_OFFSET_CH1 and OUT_OFFSET_CH2 are used as the final offset scaling stage for the desired output signal. The registers have a length of 16 bits and are two's complement-coded.

OUT_GAIN_CHx

The registers OUT_GAIN_CH1 and OUT_GAIN_CH2 are used as the final gain scaling stage for the desired output signal. They can also be used to invert the output signal. The registers have a length of 16 bits and are two's complement-coded.

Clamping Levels (CLAMP-LOW & CLAMP-HIGH)

The clamping levels CLAMP_LOW_CH1/CH2 and CLAMP_HIGH_CH1/CH2 define the maximum and minimum output values. All four registers have a length of 16 bits and are two's-complement-coded. Both clamping levels can have values between 0% and 100%.

PWM_STD_ERROR

The PWM_STD_ERROR register defines the output duty-cycle for the PWM output in case of an internal error (except MAG_LOW or under-/overvoltage error indication). The 12 LSB's are used for the 2 kHz PWM frequency and the 13 LSB's for all other frequencies. Default value is (0x0FEB = 99.5% for the 12 bit value).

SWITCHPOINT_1 and SWITCHPOINT_2 (Switch Function)

HAL/HAR 3930 also features an additional switch output for each die. It is possible to define the switching levels with the registers SWITCHPOINT_1 and SWITCHPOINT_2. The switching levels on/off can be set in percentage of full-scale of the reference signal. Further details can be found in the HAL/HAR 3930-410x User Manual.

SETUP_SWITCH (EEPROM Setting)

The setup switch register can be used to configure the switch behavior. It is possible to select between different sources for the switch function. Also the switch start-up state, the polarity, a hysteresis and the switch behavior (high-side or low-side) can be defined. The below table describes in detail the available combinations.

Table 3–1: SETUP_SWITCH

Bit No.	Function	Description
15	switch_enable	0: Switch function disabled 1: Switch output enabled
14	switch_startup_state	Internal (logic) state after POR, regarding hysteresis behavior 0: Output in OFF state 1: Output in ON state
13	switch_driven_lvl	0: Active level is high 1: Active level is low
12	switch_polarity	0: No output inversion 1: Output inverted
11:8	switch_source	0000: Primary output - OUT_1 0001: SETPOINT_OUT_1 0010: ANGLE_OUT_1 0011: Amplitude of primary output - ANGLE_AMP_1 0100: Secondary output - OUT_2 0101: SETPOINT_OUT_2 0110: ANGLE_OUT_2 0111: Amplitude of secondary output - ANGLE_AMP_2 1000: AMPLITUDE 1001: CUST_COMP_CH1 1010: CUST_COMP_CH2 1011: CUST_COMP_CH2 1100: COMP_CH1 1101: COMP_CH2 1110: COMP_CH3 1111: Chip temperature - TADJ
7:0	switch_hyst	Switch hysteresis switch_hyst = Switch hysteresis / 8 One LSB equals 8 counts (respectively 0.5 SENT counts (12bit))

Supply Voltage Supervision

As the device supports a wide supply voltage range it is beneficial to enable customer programmable under/overvoltage detection levels. The register UV_LEVEL defines the undervoltage and OV_LEVEL the overvoltage detection levels in mV. The SUPPLY_SUPERVISION register has a length of 16 bits. OV_LEVEL uses the 8 MSBs and UV_LEVEL the 8 LSBs. For both levels, 1 LSB is typically equal to 100 mV.

Customer Configuration Registers

SETUP_FRONTEND, SETUP_DATAPATH and SETUP_OUTPUT register are 16-bit registers that enable the customer to activate various functions of the sensor.

The following tables describe in detail the available combinations and resulting functions.

Table 3–2: SETUP_FRONTEND

Bit No.	Function	Description				
15	customer_lock	Customer Lock: 0: Unlocked 1: Locked				
14:13	–	Must be set to 0.				
12	setpoint_type	Setpoint type: 0: Absolute setpoints 1: Relative/differential setpoints				
11	mag_low_hi_src	Defines the source for the magnet lost detection 0: Based on AMPLITUDE RAM register 1: Based on ANGLE_AMP_1 RAM register				
10:9	modulo	Modulo operation: 00: 360° 01: Modulo 90° 10: Modulo 120° 11: Modulo 180°				
8:7	–	Reserved				
6:4	fdecsel	A/D converter sample frequency: 000: 1 kSps 001: 2 kSps 010: 4 kSps 011: 8 kSps 100 to 111: must not be set				
3:0	meas_config	Measurement setups: 0000: XY-2D-Pixel Mode ¹⁾ 0001: YZ-2D-Pixel Mode ¹⁾ 0010: XZ-2D-Pixel Mode ¹⁾ 0011: ΔXΔZ-Mode - SF compensated 0100: ΔXΔY-Mode - SF compensated 0101: ΔXΔZ-Mode - SF compensated ²⁾ 0110: 6Z-Mode- 180° rotary - SF compensated 0111: 6ZD-Mode - 360° rotary - SF compensated 1000: 3D-ATAN2-Mode - 3D measurement ¹⁾ 1001: 3D-Joystick-Mode - 3D measurement ¹⁾ 0101 & 1010 to 1111: Must not be used	Correspond. Signal Path With two channels With two channels With two channels With two channels With two channels With two channels With two channels 6 Z Hall-plates 6 ZD Hall-plates With three channels With three channels	CH1 X1 Z1 Z1 Z4-Z1 X4-X1 ΔΣZ5362 SIN 6Z SIN 6ZD Z1 Z1	CH2 Y1 Y1 X1 X4-X1 Y4-Y1 X4-X1 COS 6Z COS 6ZD X1 X1	CH3 - - - - - - - - Y1 Y1
¹⁾ HAR 3930-410x: Die 1 is using Pixel 1 with X1, Y1, Z1 and die 2 is using Pixel 2 with X4, Y4, Z4 to have both sensitive areas aligned for these modes. ²⁾ Only available in HAR 3930-4101.						

Table 3–3: SETUP_DATAPATH

Bit No.	Function	Description
15:12	nspgain_2	Gain exponent for setpoint slope in channel 2: $\text{Slope} = \text{SPGn} \times (2^{\text{nspgain_2}+1})$
11:9	nmult_2	Gain exponent for SETPOINT_IN2: $\text{SP_GAIN} = \text{SP_GAIN_CH2} \times [2^{(\text{nmult_2})}]$
8	two_channels	Activation of second output channel 0: 1 channel with setpoints 1: 2 channels with setpoints each
7:5	nmult_1	Gain exponent for SETPOINT_IN1: $\text{SP_GAIN} = \text{SP_GAIN_CH1} \times [2^{(\text{nmult_1})}]$
4:1	nspgain_1	Gain exponent for setpoint slope in channel 1: $\text{Slope} = \text{SPGn} \times (2^{\text{nspgain_1}+1})$
0	variable_setpoints	Fixed/variable setpoint selection: 0: Fixed setpoints 1: Variable setpoints

The SETUP_OUTPUT register is used to configure the two output pins OUT1/3 and OUT2/4. First of all, it is possible to define the output pin for the primary output protocol pin, i.e. OUT1/3. This can be SENT or PWM. OUT1/3 can be configured as push-pull output with different slew rates ($V_{\text{OUTmax}} < 5.5 \text{ V}$) or as an open-drain output with slew rate control for the falling edges. OUT2/4, configuration as open-drain or push-pull output follows OUT1/3.

Furthermore, this register is used to define the error behavior. In case of a PWM output, the signal frequencies and the configuration of the SENT output. Further details can be found in Table 3–4.

Table 3–4: SETUP_OUTPUT

Bit No.	Function	Description
15	primary_output	Primary output protocol selection: 0: PWM 1: SENT
14	primary_out_pin	Defines which output pin is used for the primary output 0: OUT1/3 - with slew rate control 1: OUT2/4 - no slew rate control
PWM Output (SETUP_OUTPUT[15] = 0)		
13:10	pwm_slew_rate	PWM slew rates (OUT1/3 only): 0000: slew rate control disabled: Fall = 1.5 μ s, Rise = 1.5 μ s 0001: Fall = 1.7 μ s, Rise = 1.7 μ s 0010: Fall = 2.5 μ s, Rise = 2.5 μ s 0011: Fall = 3.8 μ s, Rise = 3.8 μ s 0100: Fall = 7.4 μ s, Rise = 7.4 μ s 0101: Fall = 10.8 μ s, Rise = 10.8 μ s 0110: Fall = 14.0 μ s, Rise = 14.0 μ s 0111: Fall = 23.0 μ s, Rise = 23.0 μ s 1001...1111 are reserved for SENT Measured from/to 10% to/from 90% with $C_{LOUT} = 4.7$ nF ($V_{SUP} = 5$ V).
9:8	secondary_output	Selection of source for secondary output channel: 0x: OUT_2 (second angle) 10: ANGLE_AMP_1 11: Reserved
7	pwm_open_drain	This bit defines whether both outputs are configured as push-pull or open-drain output. 0: Push-pull 1: Open-drain
6	pwm_uvov_diag	Output behavior for undervoltage/overvoltage detection 0: Will be signalized as selected for all other diagnosis bits 1: Will be signalized with 2% duty-cycle
5	pwm_inverted	PWM inverted: 0: Active low 1: Active high
4	dual_pwm	Enables PWM on OUT1/3 and OUT2/4 to transmit information via two PWM signals: 0: Disabled 1: Enabled Note: Primary_output will be ignored in case that this bit is enabled. Both pins must be either configured as push-pull or open-drain output. Different output configuration for OUT1 and OUT2 are not supported.
3:0	pwm_frequency	Min. PWM frequency 0000: 2.0 kHz 0001: 1.5 kHz 0010: 1.0 kHz 0011: 800 Hz 0100: 550 Hz 0101: 500 Hz 0110: 250 Hz 0111: 200 Hz 1000: 150 Hz 1001: 125 Hz 1010: 100 Hz 1011 to 1111: Not allowed Typical values are 3% higher.

Table 3–4: SETUP_OUTPUT, continued

Bit No.	Function	Description	
SENT Output (SETUP_OUTPUT[15] = 1)			
13:10	sent_slew_rate	SENT slew rates (OUT1/3 only): 0000...0111 are reserved for PWM output 1000: slew rate control disabled: Fall = 1.0 μs, Rise = 1.0 μs 1001: Fall = 1.0 μs, Rise = 1.1 μs 1010: Fall = 1.7 μs, Rise = 2.1 μs 1011: Fall = 2.7 μs, Rise = 3.6 μs 1100: Fall = 5.6 μs, Rise = 7.4 μs 1101: Fall = 8.2 μs, Rise = 10.7 μs 1110: Fall = 10.7 μs, Rise = 14.0 μs 1111: Fall = 17.4 μs, Rise = 23.2 μs Measured from/to 1.1 V to/from 3.8 V with C _{LOUT} = 4.7 nF (V _{SUP} = 5 V).	
9:8	secondary_output	Secondary output selection (2 nd fast channel SENT): 0: Reserved 1: Transmission of second angle (SENT format H.1 - Table 3–6 on page 32) 2: Transmission of magnetic amplitude (SENT format H.1 - Table 3–6 on page 32) 3: Transmission of chip temperature (SENT format H.1 - Table 3–6 on page 32)	
7:4	sent_tick_time	SENT tick time selection (typ. value) 0000: 0.50 μs 0001: 1.00 μs 0010: 1.50 μs 0011: 2.00 μs 0100: 2.50 μs 0101: 2.75 μs 0110: 3.00 μs 0111: 6.00 μs 1000: 12.0 μs 1001 to 1111: reserved Note: Not all combinations of tick time and frame rate are possible.	
3:0	sent_repetition_rate	SENT frame rate 0001: 4.00 kHz 0010: 2.66 kHz 0011: 2.00 kHz 0100: 1.60 kHz 0101: 1.00 kHz 0110: 0.80 kHz 0111: 0.50 kHz	SENT message length 1000: 225 ticks 1001: 239 ticks 1010: 250 ticks 1011: 269 ticks 1100: 294 ticks 0000: 312 ticks 1101: 366 ticks 1110: 375 ticks 1111: 450 ticks

3.4. SENT Output Protocol

HAR 3930 complies with the SAEJ2716 standard rev. 4 and supports the following three frame formats:

- H.1 Format: Two 12-bit fast channels
 - A.1 Dual Throttle Position Sensors: 3 nibble position information and 3 nibble negated position information (1-position)
 - A.7 Position Sensors: 3 nibble position information and 3 nibble second position information or temperature information or magnetic-field amplitude
- H.2 Format: One 12-bit fast channel (3 nibble position information)
- H.4 Format: Secure Single Sensors with 12-bit fast channel (3 nibble position information) and 12-bit secure sensor information

All frame formats are customer selectable via bits (Table 3–5 on page 30).

Beside the supported frame formats, many other SENT interface parameters can be configured by the customer, like tick time, pause pulse, start-up behavior, transmission of error codes, serial message channel content, etc. All configurable parameters are defined in Table 3–4 and Table 3–5.

In SENT output mode, the unidirectional communication from the sensor to a receiver module (e.g. an Electronic Control Unit) occurs independently of any action of the receiver module. It does not require any synchronization signal from the receiver module and does not include a coordination signal from the controller/receiving devices.

Table 3–5: SETUP_PROTOCOL

Bit No.	Function	Description
15:14	sent_channel_format	SENT fast channel data format: 00: H.2 format: 12-bit fast channel (3 nibble position information) 01: H.4 format: Secure Single Sensors 10: H.1 format: A.1 Format for Dual Throttle Position Sensors 11: H.1 format: A.7 Format with 3 nibble position information and secondary channel
13:12	sent_low_time	SENT low time: 00: 3 ticks 01: Not allowed 10: 5 ticks 11: 6 ticks
11	sent_crc_type	0: CRC according to SAE J2716 > rev. 2 (2010) 1: CRC according to SAE J2716 rev. 1 (2008 - legacy CRC)
10	sent_status_crc	Include STATUS nibble in CRC 0: Disabled (According to SENT SAE J2716) 1: Enabled

Table 3–5: SETUP_PROTOCOL, continued

Bit No.	Function	Description
9	sent_wakeup_behavior	Definition of start-up behavior: 0: Transmission of 4094 during start-up 1: Transmission of 0 during start-up (recommended by SENT SAE J2716) Note: The status error bit is set to 1 during transmission of 0 or 4094, if sent_error_status is set to 1.
8	sent_synchronicity	Pause pulse activation 0: Disabled (SENT continuous) 1: Enabled (SENT with pause pulse)
7	sent_mag_loss	Defines the behavior of the SENT output in case of magnet loss: 0: Fast channel value 4090, 4091 or 4095 depending on sent_channel_format 1: Fast channel value = MAG_LOSS_OUTPUT register value (fast channel status bits not set and no error on slow channel)
6	sent_error_status	Definition of error status bits (see Section 3.4.4. on page 35): 0: Always zero 1: According to SAE J2716
5	sent_fast_error_codes	Definition of fast channel error codes 0: Disabled 1: Enabled
4	sent_slow_channel_format	Slow serial channel format: 0: No serial message channel 1: 12-bit enhanced serial message format
3:1	sent_slow_channel_content	Selection of which blocks have to be send in addition to block 1 in the slow channel: xx1: Block 2 x1x: Block 3 1xx: Block 4 + 5
0	sent_sdf	SENT SDF mode: 0: Send diagnosis info in front of every block 1: Send diagnosis info in front of every ID

3.4.1. H.1 Format: 6 Data Nibble Frame with Two Fast Channels

In this SENT mode the sensor transmits SENT frames with 6 data nibbles.

Two different application specific protocols are supported:

- A.1 Dual Throttle Position Sensors
- A.7 Position Sensors

In case of A.1 the first 3 data nibbles contain a 12-bit position information and the second 3 data nibbles contain the negated position of the first 3 nibbles (1-position).

Clamping of the output signal is done by the selected CLAMP_LOW and CLAMP_HIGH register values.

In case of A.7 the first 3 data nibbles contain a 12-bit position information and the second 3 data nibbles contain a 12-bit temperature information, 12-bit magnetic-field amplitude information or a second angle (customer configurable: Table 3–5). They are formatted according to Table 3–6.

Table 3–6: Nibble description for H.1 A.1 format

Pulse		Remarks
#	Description	
1	Synchronization/Calibration	It is mandatory to measure the synchronization / calibration period for calibration of the clock tick time t_{tick} at the ECU
2	4-bit Status & Communication Nibble	Status [0...1]: According to selection in Table 3–5 bit[6] Status [2...3]: According to selection in Table 3–5 bit[4]
3	4-bit Data Nibble MSN 1	Position Value [11:8]
4	4-bit Data Nibble MidN 1	Position Value [7:4]
5	4-bit Data Nibble LSN 1	Position Value [3:0]
6	4-bit Data Nibble LSN 2	Negated Position Value [3:0]
7	4-bit Data Nibble MidN 2	Negated Position Value [7:4]
8	4-bit Data Nibble MSN 2	Negated Position Value [11:8]
9	4-bit CRC Nibble	According to selection in Table 3–5 bit[11]
10	Pause Pulse	According to selection in Table 3–5 bit[8]

Table 3–7: Nibble description for H.1 A.7 format

Pulse		Remarks
#	Description	
1	Synchronization/Calibration	It is mandatory to measure the synchronization / calibration period for calibration of the clock tick time t_{tick} at the ECU
2	4-bit Status & Communication Nibble	Status [0...1]: According to selection in Table 3–5 bit[6] Status [2...3]: According to selection in Table 3–5 bit[4]
3	4-bit Data Nibble MSN 1	Position Value [11:8]
4	4-bit Data Nibble MidN 1	Position Value [7:4]
5	4-bit Data Nibble LSN 1	Position Value [3:0]
6	4-bit Data Nibble LSN 2	Value [3:0]: According to selection in Table 3–4 bits[9:8]
7	4-bit Data Nibble MidN 2	Value [7:4]: According to selection in Table 3–4 bits[9:8]
8	4-bit Data Nibble MSN 2	Value [11:8]: According to selection in Table 3–4 bits[9:8]
9	4-bit CRC Nibble	According to selection in Table 3–5 bit[11]
10	Pause Pulse	According to selection in Table 3–5 bit[8]

3.4.2. H.2 Format: 3 Data Nibble Frame with One Fast Channel

Following application specific protocol is supported:

– A.7 Position Sensors

In this mode the sensor transmits SENT frames with 3 data nibbles containing 12-bit position information. They are formatted according to Table 3–8.

Table 3–8: Nibble description for 3 data nibble frame format with one fast channel

Pulse		Remarks
#	Description	
1	Synchronization/Calibration	It is mandatory to measure the synchronization / calibration period for calibration of the clock tick time t_{tick} at the ECU
2	4-bit Status & Communication Nibble	Status [0...1]: According to selection in Table 3–5 bit[6] Status [2...3]: According to selection in Table 3–5 bit[4]
3	4-bit Data Nibble MSN 1	Position Value [11:8]
4	4-bit Data Nibble MidN 1	Position Value [7:4]
5	4-bit Data Nibble LSN 1	Position Value [3:0]
6	4-bit CRC Nibble	According to selection in Table 3–5 bit[11]
7	Pause Pulse	According to selection in Table 3–5 bit[8]

3.4.3. H.4 Format: Secure Single Sensors with 12-bit Fast Channel

The following application specific protocol is supported:

– A.7 Position Sensors

In this SENT mode, the sensor transmits SENT frames with 3 data nibbles containing 12-bit position information as well as 3 data nibbles containing 12-bit secure sensor information. The secure sensor information consists of an 8-bit rolling counter and the inverted copy of the MSN of the transmitted position information. They are formatted according to Table 3–9.

Table 3–9: Nibble description for 6 data nibble frame format with secure information

Pulse		Remarks
#	Description	
1	Synchronization/Calibration	It is mandatory to measure the synchronization / calibration period for calibration of the clock tick time t_{tick} at the ECU
2	4-bit Status & Communication Nibble	Status [0...1]: According to selection in Table 3–5 bit[6] Status [2...3]: According to selection in Table 3–5 bit[4]
3	4-bit Data Nibble MSN 1	Position Value [11:8]
4	4-bit Data Nibble MidN 1	Position Value [7:4]
5	4-bit Data Nibble LSN 1	Position Value [3:0]
6	4-bit Data Nibble MSN 2	Rolling Counter MSN
7	4-bit Data Nibble MidN 2	Rolling Counter LSN
8	4-bit Data Nibble LSN 2	Inverted Copy of Data Nibble MSN 1
9	4-bit CRC Nibble	According to selection in Table 3–5 bit[11]
10	Pause Pulse	According to selection in Table 3–5 bit[8]

3.4.4. Error Diagnostic Reporting on Fast Channel and Status Bits

The error diagnostic reporting is customer configurable. With bit [6] in the SETUP_PROTOCOL register (see Table 3–5 on page 30) different error handling can be activated:

- Always zero: Status bits are always set to zero independent from an error
- Error indication according to SAE J2716 rev. 4: The Status bits are set to one in case of “sensor error indication” or “sensor functionality and processing error indication”

In addition the diagnostic can be reported through the 12-bit payload of channel 1 and/or channel 2. Below table shows the values that will be send in case of an internal error.

Table 3–10: Error codes transmitted on fast channel 1 and/or 2

Error	Code		A.1 Mode	
	CH 1	CH 2	CH1	CH2
A.1 error code ²⁾	–	–	4095	4095
Sensor error indication ²⁾	4091	4091	N/A	N/A
Sensor functionality and processing error indication	4090	4090	–	–
Data Clamping: High	1)	1)	1)	1)
Data Clamping: Low	1)	1)	1)	1)
¹⁾ The output will clamp according to the settings for CLAMP_HIGH and CLAMP_LOW. ²⁾ In case that sent_mag_loss in the SETUP_PROTOCOL register is set to 0.				

A description with the mapping of internal errors with “Sensor error indication” and “Sensor functionality and processing error indication” can be found in Table 3–14 on page 38.

The transmission of error codes on fast channel 1 and/or 2 can be deactivated by a customer EEPROM bit (bit[5] of SETUP_PROTOCOL, Table 3–5 on page 30). The sensor will then continue to transmit measurement data. Status error bits will be transmitted according to bit[6] in the SETUP_PROTOCOL register.

3.4.5. Pause Pulse

HAL/HAR 3930 offers two options for the pause pulse. It can be enabled or disabled. In case that the pause pulse is enabled it is present at the end of every frame as defined by the SAE J2716 standard (PPC). There is no pause pulse in case it is disabled by the customer (NPP). In that case the falling edge after the CRC nibble is identical with the leading edge at the beginning of the next frame.

- **PPC:** The length of the pause pulse is automatically adjusted in order to achieve a constant frame length independent from the message content. The overall length can be defined by the sent_repetition_rate bits (SETUP_OUTPUT bits [3:0]). Two different types of PPC are supported. For the first type the overall frame length is defined in fixed multiples of the tick time and for the second type the frame length is adapted to the selected sample rate (see Table 3–4 on page 28 bits [3:0]).

Table 3–11: Message length for ticks PPC (ticks related)

SETUP_OUTPUT [3:0]	1000	1001	1010	1011	1100	0000	1101	1110	1111
ticks PPC	225	239	250	269	294	312	366	375	450

Table 3–12: Message repetition rate for PPC (sampling aligned)

SETUP_OUTPUT [3:0]	0001	0010	0011	0100	0101	0110	0111
Frequency PPC [kHz]	4.00	2.66	2.00	1.60	1.00	0.80	0.50

- **NPP:** In case of deactivated pause pulse (npp) it is possible that some samples may be transmitted twice in series due to the fact that the message time can be shorter than the sample time. Status bit 0 will then be set to one in case that a sample is transmitted twice.

3.4.6. CRC Implementation

HAL/HAR 3930 supports the recommended CRC implementation defined in SAEJ2716 rev. 4. The legacy CRC can also be activated by bit[11] in the SETUP_PROTOCOL register (see Table 3–5 on page 30). It is possible to include the status nibble in the CRC calculation. This function can be activated by bit[10] in the SETUP_PROTOCOL register as well.

3.4.7. Slow Channel: Enhanced Serial Message

HAL/HAR 3930 supports a slow channel according to the enhanced serial message with 12-bit data and 8-bit message ID. It is possible to deactivate the slow channel by changing bit[4] in the SETUP_PROTOCOL register.

3.4.8. Slow Channel: Serial Message Sequence

The device can transmit the serial message sequence shown in Table 3–13. The content/length of the serial message can be tailored by configuration bits in the SETUP_PROTOCOL register (see Table 3–5 on page 30). It is possible to activate up to five blocks. Block 1 will always be transmitted if the serial message channel is activated.

Table 3–13: Serial message sequence

Block	#	8-bit ID	Item	12-bit Data	Comment
1	1	0x01	Error Codes	(see Table 3–14 on page 38)	
	2	0x03	Sensor type		Bits 0...11 in CUSTOMER_ID0 register (12 bit) Examples: 0x050 = not specified position sensor 0x055 = position & secure channel 0x060 = angle sensor 0x064 = angle sensor + secure channel, etc.
	3	0x05	Manufacturer Code	0x007	TDK Manufacturer Code
	4	0x06	Protocol Revision	0x004	SAE J2716 rev. 4
	5	0x23	Temperature	1 to 4088 temperature data	Temperature information according to SAE J2716
2	6	0x01	Error Codes	(see Table 3–14 on page 38)	
	7	0x29	TDK-Micronas SN	8-bit MSB MIC_ID1	Right aligned
	8	0x2A	TDK-Micronas SN	8-bit LSB MIC_ID1	Right aligned
	9	0x2B	TDK-Micronas SN	8-bit MSB MIC_ID2	Right aligned
	10	0x2C	TDK-Micronas SN	8-bit LSB MIC_ID2	Right aligned
3	11	0x01	Error Codes	(see Table 3–14 on page 38)	Customer configurable
	12	0x07	Fast CH1 - X1	Fast channel 1 characteristics	Bits 0...11 in CUSTOMER_ID1 register
	13	0x08	Fast CH1 - X2	Fast channel 2 characteristics	Bits 12...15 in CUSTOMER_ID1 register Bits 0...7 in CUSTOMER_ID2 register
	14	0x09	Fast CH1 - Y1	Fast channel 1 characteristics	Bits 8...15 in CUSTOMER_ID2 register Bits 0...3 in CUSTOMER_ID3 register
	15	0x0A	Fast CH1 - Y2	Fast channel 2 characteristics	Bits 4...15 in CUSTOMER_ID3 register
4	16	0x01	Error Codes	(see Table 3–14 on page 38)	
	17	0x90	OEM Code 1 ID	ASCII character OEM Codes	Bits 0...11 in CUSTOMER_ID4 register
	18	0x91	OEM Code 2 ID	ASCII character OEM Codes	Bits 12...15 in CUSTOMER_ID4 register Bits 0...7 in CUSTOMER_ID5 register
	19	0x92	OEM Code 3 ID	ASCII character OEM Codes	Bits 8...15 in CUSTOMER_ID5 register Bits 0...3 in CUSTOMER_ID6 register
	20	0x93	OEM Code 4 ID	ASCII character OEM Codes	Bits 4...15 in CUSTOMER_ID6 register
5	21	0x01	Error Codes	(see Table 3–14 on page 38)	
	22	0x94	OEM Code 5 ID	ASCII character OEM Codes	Bits 0...11 in CUSTOMER_ID7 register
	23	0x95	OEM Code 6 ID	ASCII character OEM Codes	Bits 12...15 in CUSTOMER_ID7 register Bits 0...7 in CUSTOMER_ID8 register
	24	0x96	OEM Code 7 ID	ASCII character OEM Codes	Bits 8...15 in CUSTOMER_ID8 register Bits 0...3 in CUSTOMER_ID9 register
	25	0x97	OEM Code 8 ID	ASCII character OEM Codes	Bits 4...15 in CUSTOMER_ID9 register

Alternatively, the Error Code can be transmitted as every second slow channel message by setting bit[0] in the SETUP_PROTOCOL register (see Table 3–5 on page 30).

3.4.9. Slow Channel: Serial Message Error Codes

Diagnostic status codes are transmitted via the serial message. The 8-bit message ID for the diagnostic status code is 0x01. HAL/HAR 3930 features the error codes described in Table 3–14.

Table 3–14: Serial message error codes

Bit Position	Error Type	Fast Channel Error Code
0	Memory self-test error or checksum error	4090
1	ADC error or DSP self-test error	4090
2	Voltage regulator error	4090
3	ADC clipping	4091
4	Invalid temperature sensor values	4090
5	Signal path under/ overflow	CLAMP_LOW/CLAMP_HIGH
6	Overvoltage warning	4091
7	Undervoltage warning	4091
8	Reserved	N/A
9	Hall-plate error	4090
10	Magnet field out of range (MAG_HI, MAG_LOW) (Only if sent_mag_loss bit in the SETUP_PROTOCOL register is set to 0)	4091
11	Always set to one	-

3.4.10. Start-Up Behavior

The device can either transmit frames with value zero until a valid information is available (SAEJ2716 conform) or alternatively frames with 4094. For both cases the status error bit is set to 1 if sent_err is set to 1. The start-up behavior is customer configurable by bit[9] in the SETUP_PROTOCOL register.

3.4.11. Message Time for SENT Frames in PPC Mode

The SENT frame repetition frequency (sent_repetition_rate in SETUP_OUTPUT[3:0] register) is defined by the position sampling frequency. The selectable SENT frame repetition frequency is limited by the configured tick time, the transmitted data value and the minimum and maximum pause-pulse duration.

The tick time is customer programmable and can be selected.

Table 3–15: Available tick time ranges

Tick Time Range	EEPROM Register
0.5 µs ... 12 µs	Table 3–4 on page 28

The pulse low time can be configured to 3, 5, and 6 ticks.

4. Functional Safety

4.1. Functional Safety Manual and Functional Safety Report

The Functional Safety Manual for HAL/HAR 3930 contains the necessary information to support customers to realize a safety compliant application by integrating HAL/HAR 3930 as an ASIL C ready component, in their system. It can be integrated in automotive safety related systems up to ASIL D. The Functional Safety Manual can be provided upon request.

The Functional Safety Analysis Report describes the assumed Safety Goal, the corresponding Failure Modes as well as the Base Failure Rate for die and package according to IEC TR 62380. It can be provided based on a TDK-Micronas mission profile as well as customer mission profiles.

4.2. Integrated Diagnostic Mechanisms

HAL/HAR 3930 performs self-tests during start-up and normal operation. These increase the robustness of the device functionality by either preventing the sensor to provide wrong output signals or by reporting the failure according to SENT definition or diagnostic levels in case of PWM output. Further details about error reporting in case of SENT output see Section 3.4.9. on page 38.

For the PWM output signal the sensor is signaling errors by providing a fixed duty-cycle. This duty-cycle can be defined by the registers PWM_STD_ERROR and MAG_LOSS_OUTPUT. Additionally it is possible to report out of range events of the supply voltage with a separate duty-cycle of 2%. The behavior is customer configurable. Further details can be found in Section 3.3.2. on page 16.

■ The result of the internal diagnostics is as well available via the DIAG_X registers.

■ **Table 4–1:** DIAG_0 register

Bit no.	Description when bit is set to 1
15	DSP self-checks
14	Reserved
13	DSP checksum for ROM and RAM
12	Chip junction temperature out of range
11	Plausibility check of redundant temperature sensor
10	Hall-plate supply out of range
9	Reserved
8	Internal clock overflow supervision
7	At least one of the A/D converters delivers a stuck signal for Channel 1, 2 or 3
6	Overflow or underflow of decimation filter

Table 4–1: DIAG_0 register, continued

Bit no.	Description when bit is set to 1
5	MAG_HIGH threshold has been exceeded
4	Magnetic field amplitude is below the MAG-LOW threshold
3	The result of the position calculation (high) is out of the expected (valid) range
2	The result of the position calculation (low) is out of the expected (valid) range
1	Hall-plate current out of range
0	Reserved

Table 4–2: DIAG_1 register

Bit no.	Description when bit is set to 1
15	Reserved
14	General purpose ADC error
13	Reserved
12	Internal Bandgap error
11	Undervoltage error. Supply voltage out of range.
10	Overvoltage error. Supply voltage out of range.
9	Internal analog voltage out of range
8	Internal digital voltage out of range
Note: Bits[7:0] can not be read via the programming interface as they are triggering immediately a reset of the device.	

Note Diagnosis bits are latched in programming mode. A power-on reset is necessary to reset those bits.

5. Specifications

5.1. Outline Dimensions





Fig. 5-1:
SOIC8-1: Plastic **S**mall **O**utline **I**C package, 8 leads, gullwing bent, 150 mil
Ordering code: DJ






Fig. 5–3:
SOIC8-1: Dimensions Tape & Reel (all dimensions in mm)




Fig. 5–4: SSOP16: Tape and Reel Finishing (all dimensions in mm)

5.2. Soldering, Welding, Assembly

Information related to solderability, welding, assembly, and second-level packaging is included in the document “Guidelines for the Assembly of Micronas Packages”.

It is available on the TDK-Micronas website (<https://www.micronas.tdk.com/en/service-center/downloads>) or on the service portal (<http://service.micronas.com>).

5.3. Storage and Shelf Life Package

Information related to storage conditions of TDK-Micronas sensors is included in the document “Guidelines for the Assembly of Micronas Packages”. It gives recommendations linked to moisture sensitivity level and long-term storage.

It is available on the TDK-Micronas website (<https://www.micronas.tdk.com/en/service-center/downloads>) or on the service portal (<http://service.micronas.com>).

5.4. Size and Position of Sensitive Areas

Diameter of Hall-plate circle: $C = 2.25 \text{ mm}$




Fig. 5–5: Hall-plate configuration in case of HAR 3930




Fig. 5–6: Hall-Plate configuration in case of HAL 3930

5.5. Definition of Magnetic-Field Vectors

Die1, Die2




Fig. 5–7: Definition of magnetic-field vectors for HAR 3930

Note

Die 2 is rotated by 180° in relation to die 1. Therefore, the measurement values of magnetic-field components X and Y have opposite signs compared to die 1.




Fig. 5–8: Definition of magnetic-field vectors HAL 3930

The graph below describes the link between the external magnetic field and the sensor internal magnetic field orientation. A positive field resulting in a positive CUST_COMP register is obtained if the magnetic flux lines are in parallel to the magnetic field axis as exemplarily shown in Fig. 5–9 for the magnetic x-axis.




Fig. 5–9: Link between external magnetic field and sensor internal magnetic field orientation

5.6. Pin Connections and Short Description

Table 5–1: Pin connection SOIC8 (HAL 3930)

Pin No.	Pin Name	Type	Short Description
1	VSUP	SUPPLY	Supply voltage
2	GND	GND	Ground
3	TEST1	IN	Test (must be connected to GND)
4	OUT1	I/O	PWM/SENT output and programming
5	OUT2	OUT	PWM/SENT or Switch output (must stay open if not used)
6	TEST2	N/A	Test (must stay open)
7	TEST3	N/A	Test (must stay open)
8	TEST4	N/A	Test (must stay open)

Table 5–2: Pin connection SSOP16 (HAR 3930)

Pin No.	Pin Name	Type	Short Description
Die 1			
1	TEST1	IN	Test (must stay open)
2	TEST2	N/A	Test (must stay open)
3	VSUP1	SUPPLY	Supply voltage
4	TEST3	N/A	Test (must stay open)
5	GND1	GND	Ground
6	TEST4	N/A	Test (must be connected to GND)
7	OUT1	I/O	PWM/SENT output and programming
8	OUT2	OUT	PWM/SENT or Switch output (must stay open if not used)

Table 5–2: Pin connection SSOP16 (HAR 3930), continued

Pin No.	Pin Name	Type	Short Description
Die 2			
9	TEST5	IN	Test (must stay open)
10	TEST6	N/A	Test (must stay open)
11	VSUP2	SUPPLY	Supply voltage
12	TEST7	N/A	Test (must stay open)
13	GND2	GND	Ground
14	TEST8	N/A	Test (must be connected to GND)
15	OUT3	I/O	PWM/SENT output and programming
16	OUT4	OUT	PWM/SENT or Switch output (must stay open if not used)

5.7. Absolute Maximum Ratings

Stresses beyond those listed in the “Absolute Maximum Ratings” may cause permanent damage to the device. This is a stress rating only. Functional operation of the device at these conditions is not implied. Exposure to absolute maximum rating conditions for extended periods will affect device reliability.

This device contains circuitry to protect the inputs and outputs against damage due to high static voltages or electric fields; however, it is advised that normal precautions must be taken to avoid application of any voltage higher than absolute maximum-rated voltages to this high-impedance circuit.

All voltages listed are referenced to ground (GND).

Table 5–3: Absolute Maximum Ratings

Symbol	Parameter	Pin Name	Min.	Max.	Unit	Condition
V _{SUP}	Supply Voltage	VSUPx	–18	28	V	
			–	40	V	t < 60 s; T _A = 25 °C
V _{OUT13}	Output Voltage Output 1/3 (PWM/SENT)	OUT1/3	–	18	V	t < 96 h
			–18		V	t < 96 h; V _{SUP} ≤ 0 V
V _{OUT24}	Output Voltage Output 2/4 (Switch/PWM/SENT)	OUT2/4	–0.3	28	V	t < 96 h
V _{OUT24} –V _{SUP}	Excess of Output Voltage 2/4 over Supply Voltage	OUT2/4	–	0.3	V	t < 96 h
B _{max}	Magnetic Field	–	–1	1	T	
T _J	Junction Temperature	–	–40	190	°C	t < 96 h ¹⁾
T _A	Ambient Temperature	–	–40	160	°C	²⁾
T _{storage}	Transportation/Short Term Storage Temperature	–	–55	150	°C	Device only without packing material
V _{ESD}	ESD Protection	VSUPx, OUTx, GNDx, TESTx	–2	2	kV	³⁾
		VSUPx, GNDx	–15	15	kV	⁴⁾ ⁵⁾
		OUT1/3	–8	8	kV	⁴⁾
		OUT2/4	–4	4	kV	⁴⁾ ⁶⁾

No cumulative stress for all parameters.

¹⁾ Please contact TDK-Micronas for other temperature requirements.

²⁾ Consider current consumption, mounting condition (e.g. overmold, potting) and mounting situation for T_A and in relation to T_J.

³⁾ ESD HBM according to AEC-Q100-002 (100 pF and 1.5 kΩ).

⁴⁾ Unpowered gun test (150 pF/330 Ω) according to ISO 10605-2008.

⁵⁾ With additional protection on the PCB (according recommended application circuit with PI-Filter - Fig. 6–1 & Fig. 6–2).

⁶⁾ With additional protection on the PCB (47 nF or TVS diode).

5.8. Recommended Operating Conditions

Functional operation of the device beyond those indicated in the “Recommended Operating Conditions/Characteristics” is not implied and may result in unpredictable behavior, reduced reliability and lifetime of the device.

All voltages listed are referenced to ground (GND).

Table 5–4: Recommended Operating Conditions

Symbol	Parameter	Pin Name	Min.	Typ.	Max.	Unit	Condition
V _{SUP}	Supply Voltage	VSUPx	3.0	–	18	V	
V _{OUT13}	Output Voltage (PWM/SENT)	OUT1/3	–	–	5.5	V	Push-Pull configuration
			–	–	18	V	Open-Drain
V _{OUT24}	Output Voltage (Switch/PWM/SENT)	OUT2/4	–	–	18	V	
I _{OUT}	Output Current	OUTx	–20	–	20	mA	
R _{LOUT13}	Output Load (PWM/SENT)	OUT1/3	1	–	–	kΩ	Pull-up or pull-down resistor optional. Programming not possible with pull-down.
		OUT1/3	10	–	55	kΩ	SENT output Pull-up or pull-down resistor optional
R _{LOUT24}	Pull-up/-Down Resistor (Switch)	OUT2/4	0.5	–	–	kΩ	Pull-up or pull-down resistor optional
C _{LOUT}	Load Capacitance	OUTx	–	4.7	10	nF	
N _{PRG}	Number of Memory Programming Cycles	–	–	–	100	cycles	0 °C < T _{amb} < 55 °C
B _{AMP}	Recommended Magnetic-Field Amplitude ⁴⁾	–	10	–	150	mT	for X/Y Hall plates
		–	10	–	200	mT	for Z Hall-plates in 2D-Modes (X/Z, Y/Z) and ΔXΔZ and 3D-Modes
		–	10	–	100	mT	⁵⁾ for Z Hall-plates in 6Z- & 6ZD-Mode
T _J	Junction Temperature ¹⁾		–40	–	170	°C	for 1000 h
T _A	Ambient Temperature ²⁾		–40	–	150	°C	for V _{SUP} ≤ 5.5 V ³⁾
¹⁾ Depends on the temperature profile of the application. Please contact TDK-Micronas for life time calculations. ²⁾ Consider current consumption, mounting condition (e.g. overmold, etc.) and mounting situation for T _A and in relation to T _J . ³⁾ Supply voltages above V _{SUP} = 5.5 V may limit the max. ambient temperature range due to increased self-heating of the device. ⁴⁾ See Fig. 5–10 for further details regarding magnetic-field amplitude. ⁵⁾ Max. 200 mT for the sum (6Z-Mode) or difference (6ZD-Mode) between two opposite Hall-Plates, i.e. (Z4+Z1, Z5+Z2, Z6+Z3) or (Z4-Z1, Z5-Z2, Z6-Z3).							

Note

It is possible to operate the sensor with magnetic fields down to ±5 mT. For magnetic fields below ±10 mT, the sensor performance will be reduced.




Fig. 5–10: Definition of magnetic field amplitude

5.9. Characteristics

at $T_A = -40\text{ }^{\circ}\text{C}$ to $150\text{ }^{\circ}\text{C}$, $V_{SUP} = 3.0\text{ V}$ to 18 V (HAL 3930) & $V_{SUP} = 3.0\text{ V}$ to 5.5 V (HAR 3930), $GND = 0\text{ V}$, after programming and locking of the sensor, at Recommended Operation Conditions if not otherwise specified in the column "Conditions".

Typical Characteristics for $T_A = 25\text{ }^{\circ}\text{C}$ and $V_{SUP} = 5\text{ V}$.

Table 5–5: Characteristics

Symbol	Parameter	Pin Name	Limit Values			Unit	Conditions
			Min.	Typ.	Max.		
I _{SUP}	Supply Current	VSUPx	–	9.4	12	mA	1) Typ. value only for 6ZD-Mode for one die
I _{SUP_Start}	Start-up Current	VSUPx	–	–	20	mA	1) for V _{SUP} slope of 500 mV/μs, without external capacitor for a max. duration of 30 μs
f _{osc}	Internal Oscillator Frequency		–	32	–	MHz	
f _{sample}	Sampling Frequency		–	0.976	–	kSps	2) Configurable
			–	1.953	–		
			–	3.906	–		
			–	7.812	–		
Power-On Behavior							
V _{POR}	Power_On Reset Voltage	VSUPx	2.1	2.6	2.9	V	from low to high
V _{PORHyst}	Power_On Reset Voltage Hysteresis	VSUPx	–	125	–	mV	
Overvoltage and Undervoltage Detection							
S _{VSUP,UOV}	Scale Factor of Under-/Overvoltage Supervision Threshold	VSUPx	92	100	108	mV/LSB	Under-/Overvoltage threshold is customer configurable (see page 26). 1)
S _{VSUP,UOVhys}	Under-/Overvoltage Detection Level Hysteresis	VSUPx	–	1	–	LSB	2)
Main Outputs OUT1 & OUT3 for SENT and PWM (Push-Pull Configuration with edge shaping)							
V _{OL1/3}	Output Low Voltage	OUT1/3	–	5	8	%VSUP	V _{SUP} = 5.5 V, R _L = ∞
V _{OH1/3}	Output High Voltage	OUT1/3	91	94	–	%VSUP	V _{SUP} = 5.5 V, R _L = ∞
V _{OH,Clamp}	Output High Clamping Voltage	OUT1/3	5.2	5.7	–	V	V _{SUP} > 5.5 V, R _L = ∞
V _{OL,Clamp}	Output Low Clamping Voltage	OUT1/3	–	0.3	0.44	V	V _{SUP} > 5.5 V, R _L = ∞
R _{OUT13}	Output Resistance	OUT1/3	45	55	65	Ω	
I _{Leak13}	Output Leakage Current	OUT1/3	–25	–	25	μA	V _{OUT1} < 5.5 V
1) Characterized on small sample size (not EOL tested).							
2) Guaranteed by design.							

Table 5–5: Characteristics, continued

Symbol	Parameter	Pin Name	Limit Values			Unit	Conditions
			Min.	Typ.	Max.		
t_{rise_sym}	Rise Time of Output symmetrical to Fall Time (recommended for PWM) ¹⁾³⁾	OUT1/3	–	1.7	–	μs	pwm_slew_rates bit = 0001
			–	2.5	–		pwm_slew_rates bit = 0010
			–	3.8	–		pwm_slew_rates bit = 0011
			–	7.4	–		pwm_slew_rates bit = 0100
			–	10.8	–		pwm_slew_rates bit = 0101
			–	14.0	–		pwm_slew_rates bit = 0110
			–	23.0	–		pwm_slew_rates bit = 0111
t_{fall13}	Fall Time of Output for PWM ¹⁾³⁾	OUT1/3	–	1.7	–	μs	slew_rates bit = 0001
			–	2.5	–		slew_rates bit = 0010
			–	3.8	–		slew_rates bit = 0011
			–	7.4	–		slew_rates bit = 0100
			–	10.8	–		slew_rates bit = 0101
			–	14.0	–		slew_rates bit = 0110
			–	23.0	–		slew_rates bit = 0111
t_{rise_asym}	Rise Time of Output asymmetrical to Fall Time (recommended for SENT) ¹⁾⁴⁾	OUT1/3	–	1.1	–	μs	sent_slew_rates bit = 1001
			–	2.1	–		sent_slew_rates bit = 1010
			–	3.6	–		sent_slew_rates bit = 1011
			–	7.4	–		sent_slew_rates bit = 1100
			–	10.7	–		sent_slew_rates bit = 1101
			–	14.0	–		sent_slew_rates bit = 1110
			–	23.2	–		sent_slew_rates bit = 1111
t_{fall13}	Fall Time of Output for SENT ¹⁾⁴⁾	OUT1/3	–	1.0	–	μs	slew_rates bit = 1001
			–	1.7	–		slew_rates bit = 1010
			–	2.7	–		slew_rates bit = 1011
			–	5.6	–		slew_rates bit = 1100
			–	8.2	–		slew_rates bit = 1101
			–	10.7	–		slew_rates bit = 1110
			–	17.4	–		slew_rates bit = 1111
$I_{Oshort13_GND}$	Output Current for Short to GND	OUT1/3	–35	–25	–	mA	
$I_{Oshort13_VSUP}$	Output Current for Short to V_{SUP}	OUT1/3	–	25	35	mA	

¹⁾ Characterized on small sample size (not EOL tested).

³⁾ Measured from/to 10% to/from 90% with $C_L = 4.7$ nF. Resulting slew rates see Table 3–4.

⁴⁾ Measured from/to 1.1 V to/from 3.8 V with $C_L = 4.7$ nF & $V_{SUP} = 5$ V. Resulting slew rates see Table 3–4

Table 5–5: Characteristics, continued

Symbol	Parameter	Pin Name	Limit Values			Unit	Conditions
			Min.	Typ.	Max.		
Main Outputs OUT1 and OUT3 for PWM (Open-Drain Configuration)							
R _{OUT13}	Open-Drain Output1/3 Resistance	OUT1/3	–	70	90	Ω	
V _{OL13}	Output Low Voltage	OUT1/3	–	0.7	0.9	V	I _{Load} = 10 mA
t _{fall13}	Fall Time of Output 1/3 ¹⁾³⁾	OUT1/3	–	1.6	–	μs	slew_rates bit = x001
			–	2.4	–	μs	slew_rates bit = x010
			–	4.1	–	μs	slew_rates bit = x011
			–	8.0	–	μs	slew_rates bit = x100
			–	13.0	–	μs	slew_rates bit = x101
			–	16.7	–	μs	slew_rates bit = x110
			–	32.0	–	μs	slew_rates bit = x111
I _{Oshort13}	Output Current for Short	OUT1/3	–	25	35	mA	
I _{Leak13}	Output 1/3 Leakage Current	OUT1/3	–	–	20	μA	V _{OUT1} = 5.0 V
			–	–	140		V _{OUT1} < 18 V
Secondary Output OUT2 and OUT 4 for Switch or PWM Function (Push-Pull: High-side or Low-side)							
V _{OL24}	Output Low Voltage	OUT2/4	–	–	0.6	V	I _{Load} = 20 mA
V _{OH24}	Output High Voltage	OUT2/4	V _{SUP} – 0.6V	–	–	V	I _{Load} = –10 mA
t _{rise24}	Rise Time of Output	OUT2/4	–	120	–	ns	1) 10%/90%, C _L = 1 nF, V _{SUP} = 5 V
t _{fall24}	Fall Time of Output	OUT2/4	–	150	–	ns	1) 90%/10%, C _L = 1 nF, V _{SUP} = 5 V
I _{Oshort24_Low}	Output Current for Short to GND	OUT2/4	–50	–40	–	mA	
I _{Oshort24_High}	Output Current for Short to V _{SUP}	OUT2/4	–	40	50	mA	
I _{Leak24}	Output Leakage Current2/4	OUT2/4	–2	–	2	μA	
SENT Output Mode							
t _{tick}	SENT Tick Time	OUTx	0.48	0.50	0.52	μs	1) Configurable
			0.97	1.00	1.03	μs	
			1.45	1.50	1.55	μs	
			1.94	2.00	2.06	μs	
			2.42	2.50	2.58	μs	
			2.66	2.75	2.84	μs	
			2.91	3.00	3.09	μs	
			5.82	6.00	6.18	μs	
			11.64	12.00	12.36	μs	
1) Characterized on small sample size (not EOL tested). 3) Measured from/to 10% to/from 90% with C _L = 4.7 nF & V _{SUP} = 5 V. Resulting slew rates see Table 3–4.							

Table 5–5: Characteristics, continued

Symbol	Parameter	Pin Name	Limit Values			Unit	Conditions
			Min.	Typ.	Max.		
For 1.5 μ s tick time, 6ZD-Mode or Δ X/ Δ Z-Mode, fixed setpoints, H.4 secure channel format, pause pulse with 269 ticks (PPC) and fdecsel = 8 kSps.							
t _{S_Init}	SENT Start-up Time	OUTx	–	–	4.5	ms	1) Time until first SENT frame with init frame starts. Fig. 5–11 on page 57
t _{S_first_valid}	SENT Start-up Time till first valid Frame	OUTx	–	–	5.0	ms	1) Time until first valid SENT frame starts. Fig. 5–11 on page 57
t _{latency}	SENT average Latency	OUTx	–	0.75	–	ms	2) LP-Filter off
t _{wcresp}	SENT Step Response Time (worst case)	OUTx	–	–	1	ms	2) see Fig. 5–12
PWM Output Mode							
f _{PWM}	PWM Output Frequency	OUTx	100	–	106.2	Hz	1)
			125	–	132.5	Hz	
			150	–	159.3	Hz	
			200	–	212.4	Hz	
			250	–	265.5	Hz	
			500	–	530.9	Hz	
			550	–	584	Hz	
			800	–	849.5	Hz	
			1000	–	1061.9	Hz	
			1500	–	1592.8	Hz	
			2000	–	2123.7	Hz	
OUT _{Res}	Output Resolution	OUTx	13	–	–	bit	2) PWM freq. = 100...1500 Hz
			12	–	–	bit	2) PWM freq. = 2 kHz
t _{OSD}	Overall Signal Delay	OUTx	–	292	396	μ s	2) Overall signal delay between sensor front-end and output. Transmission time of selected PWM frequency to be added. See Fig. 5–12. fdecsel = 8 kSps LP-Filter = off
t _{P_Init}	PWM Start-up Time	OUTx	–	–	4.5	ms	1) Initial start-up time until output is ready. 2 kHz PWM frequency fdecsel = 8 kSps 6ZD - Mode Fig. 5–11 on page 57
t _{P_first_valid}	PWM Start-up Time till first Edge	OUTx	–	–	5.0	ms	1) Time until first valid rising/falling edge. 2 kHz PWM frequency 6ZD - Mode fdecsel = 8 kSps Fig. 5–11 on page 57
1) Characterized on small sample size (not EOL tested). 2) Guaranteed by design.							

Table 5–5: Characteristics, continued

Symbol	Parameter	Pin Name	Limit Values			Unit	Conditions
			Min.	Typ.	Max.		
PWM _{DC}	PWM Duty-Cycle Range	OUTx	1	–	99	%	2)
PWM _{DCFM}	PWM Duty-Cycle in Failure Mode	OUTx	According registers PWM_STD_ERROR & MAG_LOSS_OUTPUT				2) Customer configurable
PWM _{DCUV}	PWM Duty-Cycle in case of Undervoltage	OUTx	–	2.0	–	%	2) Customer configurable. Alternatively same as PWM _{DCFM} . Table 3–4 on page 28 For V _{SUP} > V _{POR}
PWM _{DCOV}	PWM Duty-Cycle in case of Overvoltage	OUTx	–	2.0	–	%	
PWM _{DCMH}	PWM Duty-Cycle in case of Magnetic Field High Detection	OUTx	–	98.0	–	%	2)
J _{PWM}	RMS PWM Jitter	OUTx	–	–	1	LSB ₁₃	1)
SOIC8 Package							
R _{thja}	Thermal Resistance Junction to Air	–	–	–	140	K/W	5) Determined with a 1S0P board
		–	–	–	93	K/W	5) Determined with a 2S2P board
R _{thjc}	Thermal Resistance Junction to Case	–	–	–	33	K/W	5) Determined with a 1S0P & 2S2P board
SSOP16 Package							
R _{thja}	Thermal Resistance Junction to Air	–	–	–	130	K/W	5) Determined with a 1S0P board
		–	–	–	91	K/W	5) Determined with a 2S2P board
R _{thjc}	Thermal Resistance Junction to Case	–	–	–	34	K/W	5) Determined with a 1S0P & 2S2P board
		–	–	–	31	K/W	5) Determined with a 2S2P board
R _{ISOL}	Isolation Resistance ¹⁾⁶⁾	GND1, GND2	4	–	–	MΩ	Between two dies (Between GND1 and GND2 pin)
¹⁾ Characterized on small sample size (not EOL tested). ²⁾ Guaranteed by design. ⁵⁾ Self-heating calculation see Section 6.1. on page 64. ⁶⁾ GND's galvanic isolation.							




Fig. 5–11: Start-up behavior for SENT and PWM output. Example for HAL 3930.




Fig. 5–12: Step response behavior. Example for HAL 3930.

5.10. Magnetic Characteristics

at $T_A = -40\text{ °C}$ to 150 °C , $V_{SUP} = 3.0\text{ V}$ to 18 V (HAL 3930) & $V_{SUP} = 3.0\text{ V}$ to 5.5 V (HAR 3930), $GND = 0\text{ V}$, after programming and locking of the sensor, at Recommended Operation Conditions if not otherwise specified in the column "Conditions".

Typical Characteristics for $T_A = 25\text{ °C}$ and $V_{SUP} = 5.0\text{ V}$.

Table 5–6: Magnetic Characteristics

Symbol	Parameter	Pin Name	Min.	Typ.	Max.	Unit	Conditions
Rotary Setup with Stray-Field Compensation (6ZD-Mode)							
ΔE_{tot}	Total Angular Error of Drifts	OUTx	−0.6	—	0.6	°	1)5) HAR 3930 $B_{AMP} = \pm 10\text{ mT}$
			−0.5	—	0.5	°	1)5) HAL 3930 $B_{AMP} = \pm 10\text{ mT}$
ΔE_{temp}	Angular Error Drift over Temperature	OUTx	−0.4	—	0.4	°	1)5) $B_{AMP} = \pm 10\text{ mT}$
ΔE_{life}	Angular Error Drift over Lifetime	OUTx	−0.4	—	0.4	°	1)5) HAR 3930 $B_{AMP} = \pm 10\text{ mT}$ After 1008 h HTOL
			−0.25	—	0.25	°	1)5) HAL 3930 $B_{AMP} = \pm 10\text{ mT}$ After 1008 h HTOL
E_{ohyst}	Angular Hysteresis Error	OUTx	—	—	0.05	°	2)
E_{noise}	Angular Noise	OUTx	—	—	0.3	°	3)5)
E_{osf}	Angular Error due to Stray-Field	OUTx	—	—	0.15	°	1)4) $B_{AMP} = \pm 10\text{ mT}$ wanted signal
Rotary Setup with Stray-Field Compensation (6Z-Mode)							
ΔE_{tot}	Total Angular Error of Drifts	OUTx	−0.30	—	0.30	°	1)6) HAR 3930 $B_{AMP} = \pm 10\text{ mT}$
			−0.25	—	0.25	°	1)6) HAL 3930 $B_{AMP} = \pm 10\text{ mT}$
ΔE_{temp}	Angular Error Drift over Temperature	OUTx	−0.20	—	0.20	°	1)6) $B_{AMP} = \pm 10\text{ mT}$
ΔE_{life}	Angular Error Drift over Lifetime	OUTx	−0.20	—	0.20	°	1)6) HAR 3930 $B_{AMP} = \pm 10\text{ mT}$ After 1008 h HTOL
			−0.15	—	0.15	°	1)6) HAL 3930 $B_{AMP} = \pm 10\text{ mT}$ After 1008 h HTOL
E_{ohyst}	Angular Hysteresis Error	OUTx	—	—	0.05	°	2)
E_{noise}	Angular Noise	OUTx	—	—	0.15	°	3)6)
E_{osf}	Angular Error due to Stray-Field	OUTx	—	—	0.1	°	1)4) $B_{AMP} = \pm 10\text{ mT}$ wanted signal
<p>All values are characterized on small sample size and 3-sigma values as long as not otherwise specified (not EOL tested).</p> <p>1) Based on Simulation Model (not EOL tested).</p> <p>2) Guaranteed by Design.</p> <p>3) Characterized on small sample size, $B_{AMP} = \pm 10\text{ mT}$, $f_{\text{dec sel}} = 2\text{ kHz}$, Low-pass filter: off, 3-sigma values (not EOL tested).</p> <p>4) Characterized on small sample size according to ISO 11452-8:2015, at 25 °C, with stray-field strength of 4 kA/m from X, Y and Z direction, 3-sigma values (not EOL tested).</p> <p>5) Referenced to an angular range of 360 °.</p> <p>6) Referenced to an angular range of 180 °.</p>							

Table 5–6: Magnetic Characteristics

Symbol	Parameter	Pin Name	Min.	Typ.	Max.	Unit	Conditions
Off-Axis Rotary Setup (ΔXY) with Stray-Field Compensation							
$SM_{\Delta XY41}$	Sensitivity Mismatch between ΔX_{41} and ΔY_{41} Channel	OUTx	–2	–	2	%	¹⁾ $T_A = 25\text{ °C}$
$Sense_{\Delta XY41}$	Sensitivity of ΔX_{41} and ΔY_{41} Channel	OUTx	121	128	135	LSB ₁₅ /mT	¹⁾ $T_A = 25\text{ °C}$
$\Delta SM_{\Delta XY41}$	Thermal Sensitivity Mismatch Drift between ΔX_{41} and ΔY_{41} Channel	OUTx	–2.5	–	2.5	%	¹⁾ Related to $T_A = 25\text{ °C}$
$Offset_{\Delta XY41}$	Offset of ΔX_{41} and ΔY_{41} Channels	OUTx	–30	–	30	LSB ₁₅	$T_A = 25\text{ °C}$
$\Delta Offset_{\Delta XY41}$	Offset Drift of ΔX_{41} and ΔY_{41} Channels	OUTx	–55	–	55	LSB ₁₅	Related to $T_A = 25\text{ °C}$ HAR 3930
			–60	–	60		Related to $T_A = 25\text{ °C}$ HAL 3930
$\Delta SM_{\Delta XY41\text{life}}$	Relative Sensitivity Mismatch Drift between ΔX_{41} and ΔY_{41} Channels over life time	OUTx	–	1.0	–	%	¹⁾ After 1008 h HTOL
$\Delta Offset_{\Delta XY41\text{life}}$	Offset Drift of ΔX_{41} and ΔY_{41} Channel over life time	OUTx	–	30	–	LSB ₁₅	After 1008 h HTOL
$SF_{R\Delta XY41}$	Stray-Field Rejection in ΔX_{41} and ΔY_{41} Direction	OUTx	98.5	–	–	%	
$E_{\text{phase}\Delta XY41}$	Phase Error between ΔX_{41} and ΔY_{41} Channel	OUTx	–	± 2.9	–	°	¹⁾ between ΔX_{41} and ΔY_{41} axis
$E_{\Delta XY41,\text{noise}}$	Digital Noise of ΔX_{41} and ΔY_{41} Hall-Plates Channel	OUTx	–	2.4	–	LSB ₁₅	⁷⁾
Linear Movement Setup (ΔXZ) with Stray-Field Compensation							
$SM_{\Delta XZ41}$	Sensitivity Mismatch between ΔX_{41} and ΔZ_{41} Channel	OUTx	–5	–	5	%	¹⁾ $T_A = 25\text{ °C}$
$Sense_{\Delta XZ41}$	Sensitivity of ΔX_{41} and ΔZ_{41} Channel	OUTx	121	128	135	LSB ₁₅ /mT	¹⁾ $T_A = 25\text{ °C}$
$\Delta SM_{\Delta XZ41}$	Thermal Sensitivity Mismatch Drift between ΔX_{41} and ΔZ_{41} Channel	OUTx	–2.5	–	2.5	%	¹⁾ Related to $T_A = 25\text{ °C}$
$Offset_{\Delta X41}$	Offset of ΔX_{41} Channel	OUTx	–30	–	30	LSB ₁₅	$T_A = 25\text{ °C}$
$Offset_{\Delta Z41}$	Offset of ΔZ_{41} Channel	OUTx	–12	–	12	LSB ₁₅	$T_A = 25\text{ °C}$
$\Delta Offset_{\Delta X41}$	Offset Drift of ΔX_{41} Channel	OUTx	–55	–	55	LSB ₁₅	Related to $T_A = 25\text{ °C}$ HAR 3930
			–60	–	60		Related to $T_A = 25\text{ °C}$ HAL 3930
$\Delta Offset_{\Delta Z41}$	Offset Drift ΔZ_{41} Channel	OUTx	–15	–	15	LSB ₁₅	Related to $T_A = 25\text{ °C}$
$\Delta SM_{\Delta XZ41\text{life}}$	Relative Sensitivity Mismatch Drift between ΔX_{41} and ΔZ_{41} Channel over life time	OUTx	–	± 3.0	–	%	¹⁾ After 1008 h HTOL
All values are characterized on small sample size and 3-sigma values as long as not otherwise specified (not EOL tested). ¹⁾ Based on Simulation Model (not EOL tested). ⁴⁾ Characterized on small sample size according to ISO 11452-8:2015, at 25°C, with stray-field strength of 4 kA/m from X, Y and Z direction, 3-sigma values (not EOL tested). ⁷⁾ Characterized on small sample size, 1-sigma values of COMP_CHx, fdecsel = 2 kHz, Low-pass filter: off (not EOL tested).							

Table 5–6: Magnetic Characteristics

Symbol	Parameter	Pin Name	Min.	Typ.	Max.	Unit	Conditions
$\Delta\text{Offset}_{\Delta X41\text{life}}$	Offset Drift of ΔX_{41} Channel over life time	OUTx	–	30	–	LSB ₁₅	After 1008 h HTOL
$\Delta\text{Offset}_{\Delta Z41\text{life}}$	Offset Drift of ΔZ_{41} Channel over life time	OUTx	–	7	–	LSB ₁₅	After 1008 h HTOL
$\text{SF}_{R\Delta X41}$	Stray-Field Rejection in ΔX_{41} Direction	OUTx	98.5	–	–	%	⁴⁾ $T_A = 25^\circ\text{C}$
$\text{SF}_{R\Delta Z41}$	Stray-Field Rejection in ΔZ_{41} Direction	OUTx	98.5	–	–	%	⁴⁾ $T_A = 25^\circ\text{C}$
$E_{\text{opphase}\Delta XZ41}$	Phase Error between ΔX_{41} and ΔZ_{41} Channel	OUTx	–	± 2.2	–	°	between ΔX_{41} and ΔZ_{41} axis ¹⁾
$E_{\Delta X41,\text{noise}}$	Digital Noise of ΔX_{41} Hall-Plates Channel	OUTx	–	2.4	–	LSB ₁₅	⁷⁾
$E_{\Delta Z41,\text{noise}}$	Digital Noise of ΔZ_{41} Hall-Plates Channel	OUTx	–	2.6	–	LSB ₁₅	⁷⁾
Linear Movement Setup ($\Delta X\Delta Z$) with Stray-Field Compensation - HAR 3930-4101							
$\text{SM}_{\Delta X\Delta Z}$	Sensitivity Mismatch between ΔX and ΔZ Channel	OUTx	–5	–	5	%	¹⁾ $T_A = 25^\circ\text{C}$
$\text{Sense}_{\Delta X\Delta Z}$	Sensitivity of ΔX and ΔZ Channel	OUTx	121	128	135	LSB ₁₅ /mT	¹⁾ $T_A = 25^\circ\text{C}$
$\Delta\text{SM}_{\Delta X\Delta Z}$	Thermal Sensitivity Mismatch Drift between ΔX and ΔZ Channel	OUTx	–3	–	3	%	¹⁾ Related to $T_A = 25^\circ\text{C}$
$\text{Offset}_{\Delta X}$	Offset of ΔX Channel	OUTx	–30	–	30	LSB ₁₅	$T_A = 25^\circ\text{C}$
$\text{Offset}_{\Delta Z}$	Offset of ΔZ Channel	OUTx	–36	–	36	LSB ₁₅	$T_A = 25^\circ\text{C}$
$\Delta\text{Offset}_{\Delta X}$	Offset Drift of ΔX Channel	OUTx	–55	–	55	LSB ₁₅	Related to $T_A = 25^\circ\text{C}$
$\Delta\text{Offset}_{\Delta Z}$	Offset Drift ΔZ Channel	OUTx	–15	–	15	LSB ₁₅	Related to $T_A = 25^\circ\text{C}$
$\Delta\text{SM}_{\Delta X\Delta Z\text{life}}$	Relative Sensitivity Mismatch Drift between ΔX and ΔZ Channel over life time	OUTx	–	± 3	–	%	¹⁾ After 1008 h HTOL
$\Delta\text{Offset}_{\Delta X\text{life}}$	Offset Drift of ΔX Channel over life time	OUTx	–	30	–	LSB ₁₅	After 1008 h HTOL
$\Delta\text{Offset}_{\Delta Z\text{life}}$	Offset Drift of ΔZ Channel over life time	OUTx	–	7	–	LSB ₁₅	After 1008 h HTOL
$\text{SFR}_{\Delta X}$	Stray-Field Rejection in ΔX Direction	OUTx	98.5	–	–	%	⁴⁾ $T_A = 25^\circ\text{C}$
$\Delta\text{SFR}_{\Delta X}$	Drift of Stray-Field Rejection in ΔX Direction over temperature	OUTx	–	–	1	%	⁴⁾ Related to $T_A = 25^\circ\text{C}$
$\Delta\text{SFR}_{\Delta X\text{life}}$	Drift of Stray-Field Rejection in ΔX Direction over life time	OUTx	–	–	0.6	%	⁴⁾ After 1008 h HTOL
$\text{SFR}_{\Delta Z}$	Stray-Field Rejection in ΔZ Direction	OUTx	98.5	–	–	%	⁴⁾ $T_A = 25^\circ\text{C}$
$\Delta\text{SFR}_{\Delta Z}$	Drift of Stray-Field Rejection in ΔZ Direction over temperature	OUTx	–	–	1	%	⁴⁾ Related to $T_A = 25^\circ\text{C}$
All values are characterized on small sample size and 3-sigma values as long as not otherwise specified (not EOL tested). ¹⁾ Based on Simulation Model (not EOL tested). ⁴⁾ Characterized on small sample size according to ISO 11452-8:2015, at 25°C , with stray-field strength of 4 kA/m from X, Y and Z direction, 3-sigma values (not EOL tested). ⁷⁾ Characterized on small sample size, 1-sigma values of COMP_CHx, fdecsel = 2 kHz, Low-pass filter: off (not EOL tested).							

Table 5–6: Magnetic Characteristics

Symbol	Parameter	Pin Name	Min.	Typ.	Max.	Unit	Conditions
$\Delta SFR_{\Delta 4Zlife}$	Drift of Stray-Field Rejection in $\Delta 4Z$ Direction over life time	OUTx	–	–	1	%	⁴⁾ After 1008 h HTOL
$E_{\text{opphase}\Delta X4Z}$	Phase Error between ΔX and $\Delta 4Z$ Channel	OUTx	–	± 2.2	–	°	between ΔX and $\Delta 4Z$ axis ¹⁾
$E_{\Delta X,noise}$	Digital Noise of ΔX Hall-Plates Channel	OUTx	–	2.4	–	LSB ₁₅	⁷⁾
$E_{\Delta 4Z,noise}$	Digital Noise of $\Delta 4Z$ Hall-Plates Channel	OUTx	–	3.6	–	LSB ₁₅	⁷⁾
2D-Mode (XY, XZ, YZ) & 3D-ATAN2-Mode & 3D-Joystick-Mode w/o Stray-Field Compensation							
SM_{XYZ}	Sensitivity Mismatch between X or Y and Z Channel	OUTx	–4	–	4	%	$T_A = 25\text{ °C}$
SM_{XY}	Sensitivity Mismatch between X and Y Channel	OUTx	–2	–	2	%	$T_A = 25\text{ °C}$
$Sense_{XYZ}$	Sensitivity of X,Y and Z Hall-plate	OUTx	123	128	133	LSB ₁₅ /mT	$T_A = 25\text{ °C}$
ΔSM_{XYZ}	Thermal Sensitivity Mismatch Drift between X or Y and Z Hall-plates	OUTx	–2.7	–	2.7	%	Related to $T_A = 25\text{ °C}$
ΔSM_{XY}	Thermal Sensitivity Mismatch Drift between X and Y Hall-plates	OUTx	–2	–	2	%	Related to $T_A = 25\text{ °C}$
$Offset_{XY}$	Offset of X and Y Hall-plates	OUTx	–20	–	20	LSB ₁₅	$T_A = 25\text{ °C}$
$Offset_Z$	Offset of Z Hall-plate	OUTx	–10	–	10	LSB ₁₅	$T_A = 25\text{ °C}$
$\Delta Offset_{XY}$	Offset Drift of X and Y Hall-plates	OUTx	–40	–	40	LSB ₁₅	Related to $T_A = 25\text{ °C}$
$\Delta Offset_Z$	Offset Drift of Z Hall-plate	OUTx	–12	–	12	LSB ₁₅	Related to $T_A = 25\text{ °C}$
$\Delta SM_{XYZlife}$	Relative Sensitivity Mismatch Drift between X, Y and Z Hall-plates over life time	OUTx	–	4.7	–	%	After 1008 h HTOL
$\Delta Offset_{XYlife}$	Offset Drift of X and Y Hall-plates over life time	OUTx	–	30	–	LSB ₁₅	After 1008 h HTOL
$\Delta Offset_Zlife$	Offset Drift of Z Hall-plate over life time	OUTx	–	5	–	LSB ₁₅	After 1008 h HTOL
$E_{\text{opphase}XYZ}$	Phase Error between X, Y and Z Hall-plates	OUTx	–	± 2.0	–	°	XY axis
			–	± 1.6	–	°	XZ axis
			–	± 2.5	–	°	YZ axis
$E_{XYZ,noise}$	Digital Noise of X, Y or Z Hall-Plates Channel	OUTx	–	2.2	–	LSB ₁₅	⁷⁾
<p>All values are characterized on small sample size and 3-sigma values as long as not otherwise specified (not EOL tested).</p> <p>⁴⁾ Characterized on small sample size according to ISO 11452-8:2015, at 25°C, with stray-field strength of 4 kA/m from X,Y and Z direction, 3-sigma values (not EOL tested).</p> <p>⁷⁾ Characterized on small sample size, 1-sigma values of COMP_CHx, fdecsel = 2 kHz, Low-pass filter: off (not EOL tested).</p>							

5.11. Temperature Sensor

at $T_A = -40\text{ °C}$ to 150 °C , $V_{SUP} = 3.0\text{ V}$ to 18 V , $GND = 0\text{ V}$, after programming and locking of the sensor, at Recommended Operation Conditions if not otherwise specified in the column “Conditions”.

Typical Characteristics for $T_A = 25\text{ °C}$ and $V_{SUP} = 5.0\text{ V}$.

Table 5–7: Temperature Sensor

Symbol	Parameter	Pin No.	Min.	Typ.	Max.	Unit	Conditions
TADJ _{Gain}	Gain of Temperature Sensor	OUT1/3	–	89.25	–	LSB ₁₅ /°C	¹⁾ for TADJ register
TADJ _{Offset}	Temperature Sensor Offset	OUT1/3	–	3720	–	LSB ₁₅	¹⁾ for TADJ register
TSENT _{Gain}	Gain of Temperature Sensor for SENT Output	OUT1/3	–	8.1	–	LSB ₁₂ /°C	¹⁾ SENT Slow Channel
TSENT _{Offset}	Temperature Sensor Offset for SENT Output	OUT1/3	–	565.3	–	LSB ₁₂	¹⁾ SENT Slow Channel
ΔT_{Lin}	Temperature Sensor Linearity Error	OUT1/3	–2	–	2	°C	²⁾
ΔT_{Acc}	Temperature Sensor Accuracy Error	OUT1/3	–5	–	5	°C	²⁾
¹⁾ Not EOL tested. ²⁾ Characterized on small sample size, 3-sigma values. Not EOL tested.							

6. Application Notes

6.1. Ambient Temperature

Due to the internal power dissipation, the temperature on the silicon chip (junction temperature T_J) is higher than the temperature outside the package (ambient temperature T_A).

$$T_J = T_A + \Delta T$$

The maximum ambient temperature is a function of power dissipation, maximum allowable die temperature and junction to ambient thermal resistance (R_{thja}).

The power dissipation is calculated as $P = V_{SUPx} \times I_{SUPx}$. This value must be multiplied by a factor of two in case of HAR 3930.

The junction to ambient thermal resistance R_{thja} is specified in Section 5.9. on page 52.

The difference between junction and ambient air temperature is expressed by the following equation (at static conditions and continuous operation):

$$\Delta T = P \times R_{thjX}$$

The X represents junction to air, case or solder point.

For worst-case calculation, use the max. parameters for I_{SUP} and R_{thjX} , and the max. value for V_{SUP} from the application.

Note	The calculated self-heating of the device is only valid for the R_{th} test boards. Depending on the application setup the final results in an application environment might deviate from these values.
-------------	---

6.2. EMC and ESD

Please contact TDK-Micronas for detailed information on EMC and ESD performance.

6.3. Application Circuits




Fig. 6–1: Recommended application circuit for HAR 3930

Table 6–1: Recommended external components for HAR 3930 in SSOP16 package

Component	Typ. value	Comment
C ₁ , C ₅	470 nF	
C ₂ , C ₆	4.7 nF	
C ₃ , C ₇	4.7 nF	
C ₄ , C ₈	4.7 nF	Optional for improved EMC performance.
R ₁ , R ₂	120 Ω	




Fig. 6–2: Recommended application circuit for HAL 3930

Table 6–2: Recommended external components for HAL 3930 in SOIC8 package

Component	Typ. value	Comment
C ₁	470 nF	
C ₂	4.7 nF	
C ₃	4.7 nF	
C ₄	4.7 nF	Optional for improved EMC performance.
R ₁	120 Ω	

6.4. Recommended Pad Size




Fig. 6–3: Pad size recommendation for SOIC8 package (all dimensions in mm)




Fig. 6–4: Pad size recommendation for SSOP16 Package (all dimensions in mm)

7. Programming of the Sensor

HAL/HAR 3930 features two different customer modes. In **Application Mode** the sensor provides a digital output signal according SENT standard or by transmission of PWM signals. In **Programming Mode (Listen Mode)** it is possible to change the register settings of the sensor.

After power-up the sensor is always operating in the **Application Mode**. It is switched to the **Programming Mode** by a BiPhase-M protocol via output voltage modulation. Therefore the programming device needs to provide a long sync pulse at the output pin.

7.1. Programming Interface

In Programming Mode HAL/HAR 3930 is addressed by modulating a serial telegram on the sensor's output pin. The sensor answers with a modulation of the output voltage.

A logical "0" is coded as no level change within the bit time. A logical "1" is coded as a level change of typically 50% of the bit time. After each bit, a level change occurs (see Fig. 7–1).

The serial telegram is used to transmit the memory content, error codes and digital values of the angle information from and to the sensor.




Fig. 7–1: Definition of logical 0 and 1 bit

Table 7–1: Telegram parameters for the Host (All voltages are referenced to GND.)

Symbol	Parameter	Pin No.	Limit Values			Unit	Test Conditions
			Min.	Typ.	Max.		
t_{h_bbit}	Host Biphas bit time	OUT1	0.01	–	1.1	ms	
SR	Host slew rate Biphas protocol	OUT1	10	–	–	V/ μ s	¹⁾ For recommended application circuit
V_{H_OUTL}	Host OUT pin voltage for low level during programming	OUT1	–	–	0.8	V	
V_{H_OUTH}	Host OUT pin voltage for high level during programming	OUT1	2.4	–	–	V	
$V_{SUPProgr}$	V_{SUP} Voltage for memory programming	VSUP	$V_{SUP,min.}$	–	$V_{SUP,max.}$	V	
¹⁾ Not EOL tested.							

7.2. Programming Environment and Tools

For the programming of HAL/HAR 3930 during product development a programming tool including hardware and software is available on request. It is recommended to use the TDK-Micronas tool kit (TDK MSP V1.x and LabView Programming Environment) in order to facilitate the product development. The details of programming sequences are content of the HAL/HAR 393x-4100 Programming Guide.

7.3. Programming Information

For production and qualification tests, it is mandatory to set the LOCK bit to one after final adjustment and programming of HAL/HAR 3930.

Before locking the device, it is recommended to read back all register values to ensure that the intended data is correctly stored in the sensor's memory. Alternatively, it is also possible to cross-check the sensor output signal with the intended output behavior.

The success of the LOCK process shall be checked by reading the status of the LOCK bit after locking.

Even after locking the device it is still possible to read the memory content.

It is also mandatory to check the acknowledge of the sensor after each write and store sequence to verify if the programming of the sensor was successful.

ElectroStatic Discharges (ESD) may disturb the programming pulses. Please take precautions against ESD.

Note

A description of the communication protocol and the programming of the sensor is available in a separate document HAL/HAR 393x-4100 Programming Guide.

8. Document History

1. Data Sheet: "HAL/HAR 3930-4100 Stray-Field Robust 3D Position Sensor with Digital Output Interfaces", July 21, 2023, DSH000233_001EN. First release of the Data Sheet.
Describing Configuration-ID releases: 4100 (for mass production)

2. Data Sheet: "HAL/HAR 3930-410x Stray-Field Robust 3D Position Sensor with Digital Output Interfaces", Nov. 12, 2024, DSH000233_002EN. Second release of the Data Sheet.
Describing Configuration-ID releases: = 410x

Major changes compared to previous Data Sheet:

- HAR 3930-4101 added as new device
- Update of SSOP-16 package drawing